



Pedestal, 2-Gang, Aluminum

By Hubbell Wiring Device-Kellems
Catalog # [FR80AL](#)

In-Floor Delivery Systems, Fire-Rated Poke-Throughs, Pedestal Series, Pedestal, 2-Gang, Aluminum



Features

- 1-4 hour fire rating (1-3 hour for steel floor units and concrete topping, D900 Series Design)
- For 2 ¼ in. to 7 in. floor thickness
- Approved for use in the City of Chicago

General

Color	Natural
EU RoHS Indicator	No
Finish Type	Aluminum
Item Type	Above Floor Service Fittings
Material	Aluminum
Material - Mounting Hardware	On PT7XC Through Floor Fitting
Mounting Hardware	Included
OEM Brand Name	Hubbell Wiring Device-Kellems
Performance	Electrical - Service Pedestal Construction - Heavy gauge aluminum frame with satin anodized aluminum housing with 302/304 stainless steel face plates
Style	Pedestals
UPC	783585396323

Dimensions

Display Size Standard Sized Product

Logistics

Carton Quantity 5

Product Assets

[Catalog Page - Wiring Q-35 Catalog page](#)
[Catalogs - Wiring Full Catalog](#)
[Installation Manuals - WIRING_PD1901_INSTALLINST](#)
[Sales Drawings - WDK_FR80AL_DRAWING_PDF](#)
[Warranty - Industrial & Commercial Products](#)

Related Products

[SS309S - LO-CON Series, Plate, 1.40" Opening, Stainless Steel](#)
[SS309D - LO-CON Series, Plate, Duplex, Stainless Steel](#)
[SS309T - LO-CON Series, Plate, Telephone, Stainless Steel](#)
[SS309SF - LO-CON Series, Plate, Furniture Feed, Stainless Steel](#)
[SS309B - LO-CON Series, Plate, Blank, Stainless Steel](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
WDK-FR80AL-SPEC-EN | REV 5/2023