



Switches and Lighting Control, Fluorescent Starter, 25/22W CIRC

By Hubbell Wiring Device-Kellems
Catalog # [FS25](#)

Switches and Lighting Control, Fluorescent Starter, 25/22W
CIRC



Features

- Rugged construction
- Operates over a wide temperature range
- Neostart lights in dual lamp circuit uniformly and quickly

General

Color	Gray
Item Type	Neo-Start Fluorescent Starter
Lamp Type	Fluorescent
Material - Mounting Hardware	Twist-In
OEM Brand Name	Hubbell Wiring Device-Kellems
Start Type	Neo Start
UPC	783585750088

Dimensions

Dimensions	1.5 in x 0.7 in x 0.7 in
Height	0.7 in
Length	1.5 in
Width	0.7 in

Electrical Ratings

Frequency Rating	60 Hz
Voltage Rating	Determined by the ballasts kV
Wattage	13, 30 and 40 Wall Lamps

Certifications and Compliance

Industry Standard(s)	UL Listed
----------------------	-----------

Logistics

Carton Quantity	25
-----------------	----

Product Assets

[Catalog Page - Wiring_Catalog_CC4_CatPage](#)
[Catalogs - Wiring Full Catalog](#)
[Warranty - Industrial & Commercial Products](#)

Related Products

[FS25 - Switches and Lighting Control, Fluorescent Starter, 25/22W CIRC](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
WDK-FS25-SPEC-EN | REV 5/2023