



Wiring Device-Kellems

Switches and Lighting Control, Fluorescent Starter, 13-30-40W

By Hubbell Wiring Device-Kellems
Catalog # FS4

Switches and Lighting Control, Fluorescent Starter, 13-30-40W



General

Color	Gray
Item Type	Neo-Start Fluorescent Starter
Lamp Type	Fluorescent
Material - Mounting Hardware	Twist-In
OEM Brand Name	Hubbell Wiring Device-Kellems
Start Type	Neo Start
UPC	783585750033

Dimensions

Dimensions	1.5 in x 0.7 in x 0.7 in
Height	0.7 in
Length	1.5 in
Width	0.7 in

Electrical Ratings

Frequency Rating	60 Hz
Voltage Rating	Determined by the balasts kV
Wattage	4, 6 and 8 Watt Lamps

Certifications and Compliance

Industry Standard(s)	UL Listed
----------------------	-----------

Logistics

Carton Quantity	25
-----------------	----

Product Assets

- [Catalog Page - Wiring_Catalog_CC4_CatPage](#)
- [Catalogs - Wiring Full Catalog](#)
- [Warranty - Industrial & Commercial Products](#)

Related Products

[FS4 - Switches and Lighting Control, Fluorescent Starter, 13-30-40W](#)



A proud member of the Hubbell Family.