



Switches and Lighting Control, Fluorescent Starter, 4-6-8W

By Hubbell Wiring Device-Kellems
Catalog # [FS5](#)

Switches and Lighting Control, Fluorescent Starter, 4-6-8W



General

| | |
|------------------------------|-------------------------------|
| Color | Gray |
| Item Type | Neo-Start Fluorescent Starter |
| Lamp Type | Fluorescent |
| Material - Mounting Hardware | Twist-In |
| OEM Brand Name | Hubbell Wiring Device-Kellems |
| Start Type | Neo Start |
| UPC | 783585750057 |

Dimensions

| | |
|------------|--------------------------|
| Dimensions | 1.5 in x 0.7 in x 0.7 in |
| Height | 0.7 in |
| Length | 1.5 in |
| Width | 0.7 in |

Electrical Ratings

| | |
|------------------|-----------------------------------|
| Frequency Rating | 60 Hz |
| Voltage Rating | Determined by the balasts kV |
| Wattage | 22 Watt Circ and 22 Watt Standard |

Certifications and Compliance

| | |
|----------------------|-----------|
| Industry Standard(s) | UL Listed |
|----------------------|-----------|

Logistics

| | |
|-----------------|----|
| Carton Quantity | 25 |
|-----------------|----|

Product Assets

[Catalog Page - Wiring_Catalog_CC4_CatPage](#)
[Catalogs - Wiring Full Catalog](#)
[Warranty - Industrial & Commercial Products](#)

Related Products

[FS5 - Switches and Lighting Control, Fluorescent Starter, 4-6-8W](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
WDK-FS5-SPEC-EN | REV 5/2023