



Circuit Guard® Extra Heavy Duty Portable Straight Blade GFCI with Automatic Set, 30A, 120V AC, 50', Yellow

By Hubbell Wiring Device-Kellems
Catalog # [GFP1313](#)



Power Protection Products, GFCI High Amperage Portables, Industrial/Commercial, Auto Set, 30A 120V AC, 50' Cord Length, 4-6 mA Trip Level, Y ellow.

Features

- Electromagnetic Latching Mechanism
- Trips if ground and neutral touch at load side
- Red blinking light plus optional audible alarm
- Open neutral protection Trips upon loss of neutral

Application

Line Cord Only No Devices

General

Color	Yellow
Construction	Fabricated
EU RoHS Indicator	No
Item Type	Industrial Grade
Material - Insulation	Elastomer
Material - Jacket	PVC
OEM Brand Name	Hubbell Wiring Device-Kellems
Performance	<ul style="list-style-type: none"> • Electrical - Dielectric Withstand - 1500 VRMS across contact, 4000 VRMS between conductors & enclosure • Electrical - Operating Voltage Range - 85% to 110% • Electrical - Rated Voltage - 120V AC, 240V AC, 120/240V AC, 3Ø 250V AC, 3Ø 120/208V AC • Electrical - Surge Withstand - 6000V impulse, 0.5 ms rise time 100kHz ringing frequency • Environmental - Construction - Industrial grade design • Environmental - Housing Rating - UL Type 4X • Environmental - Leakage Current - At 93% Humidity leakage current is zero • Environmental - Operating

Dimensions

Outside Diameter	0.335
Weight	12.95 lb

Electrical Ratings

Amperage Rating	30 A
Connectivity	Plug-In
Current / Amperage Rating	30 A
Current Rating	30 A
Voltage Rating	120 VAC
Voltage Rating Description	120 VAC

Conductor Related

Conductor Size	#10 AWG
Conductor Type	Copper
Number Of Conductors	3
Strands	Multi

Certifications and Compliance

Industry Standard(s)	UL Listed
----------------------	-----------

Logistics

Carton Quantity	5
-----------------	---

Product Assets

[Catalog Page - Wiring L-20 Catalog page](#)
[Catalogs - Wiring Full Catalog](#)
[Installation Manuals - WIRING_PD1827_INSTALLINST](#)
[Literature - WIRING_WLFVM034](#)
[Literature - Pulp & Paper Solutions](#)
[Sales Drawings - WDK_GFP13_DRAWINGS_PDF](#)
[Warranty - Industrial & Commercial Products](#)

Related Products

[GFP1315 - Circuit Guard® Extra Heavy Duty Portable Straight Blade GFCI with Automatic Set, 30A, 120V AC, 6', Yellow](#)
[GFP1301 - Circuit Guard® Extra Heavy Duty Portable Straight Blade GFCI with Manual Set, 30A, 120V AC, 2', Black](#)
[GFP1312 - Circuit Guard® Extra Heavy Duty Portable Straight Blade GFCI with Automatic Set, 30A, 120V AC, 25', Yellow](#)
[GFP1303 - Circuit Guard® Extra Heavy Duty Portable Straight Blade GFCI with Manual Set, 30A, 120V AC, 50', Black](#)
[GFP1302 - Circuit Guard® Extra Heavy Duty Portable Straight](#)

- Environmental - Operating Temperature - -35°C to 66°C, -30°F to 150°F.
- Environmental - Type - Meets UL943 Class A GFCI

Series	Extra Heavy Duty
Style	Automatic Set
Temperature Rating	-35 Degrees C to 66 Degrees C (-30 Degrees F to 150 Degrees F)
Type	Portable, Straight Blade
UPC	783585005744



A proud member of the Hubbell Family.