

Circuit Guard® Extra Heavy Duty
Portable Straight Blade GFCI with
Manual Set, 30A, 120/240V AC, 2',
Black

By Hubbell Wiring Device-Kellems
Catalog # [GFP3305](#)



Power Protection Products, GFCI High Amperage Portables,
Industrial/Commercial, Manual Set, 30A 120/240V AC, 6' Cord
Length, 4-6 mA Trip Level, Black.

Application

Line Cord Only No Devices

Performance

- Electrical - Dielectric Withstand - 1500 VRMS across contact, 4000 VRMS between conductors & enclosure
- Electrical - Operating Voltage Range - 85% to 110%
- Electrical - Rated Voltage - 120V AC, 240V AC, 120/240V AC, 3Ø 250V AC, 3Ø 120/208V AC
- Electrical - Surge Withstand - 6000V impulse, 0.5 ms rise time 100kHz ringing frequency
- Environmental - Construction - Industrial grade design
- Environmental - Housing Rating - UL Type 4X
- Environmental - Leakage Current - At 93% Humidity leakage current is zero
- Environmental - Operating Temperature - -35°C to 66°C, -30°F to 150°F.
- Environmental - Type - Meets UL943 Class A GFCI

General

| | |
|-----------------------|--|
| Catalog Number | GFP3305 |
| Color | Black |
| Construction | Fabricated |
| EU RoHS Indicator | No |
| Item Type | Industrial Grade |
| Material - Insulation | Elastomer |
| Material - Jacket | PVC |
| OEM Brand Name | Hubbell Wiring Device-Kellems |
| Series | Extra Heavy Duty |
| Specifications | <ul style="list-style-type: none">Cord Type - 2-50', 10/3 SJGOOW. 100', 8/3 SEOWLabel Color - Black background with yellow letteringResponse Time - .025 sec. MaxSwitch Interface - Double InsulatedTrip Level - 4 to 6 mA |

| | |
|--------------------|--|
| Style | Unit Color - Gray with black cover |
| Temperature Rating | Manual Set |
| | -35 Degrees C to 66 Degrees C (-30 Degrees F to 150 Degrees F) |
| Type | Portable, Straight Blade |
| UPC | 783585521169 |

Dimensions

| | |
|------------------|--------|
| Outside Diameter | 0.335 |
| Weight | 4.5 lb |

Electrical Ratings

| | |
|----------------------------|-------------|
| Amperage Rating | 30 A |
| Connectivity | Plug-In |
| Current / Amperage Rating | 30 A |
| Current Rating | 30 A |
| Voltage Rating | 120/240 VAC |
| Voltage Rating Description | 120/240 VAC |

Conductor Related

| | |
|----------------------|---------|
| Conductor Size | #10 AWG |
| Conductor Type | Copper |
| Number of Conductors | 4 |
| Strands | Multi |

Certifications And Compliance

| | |
|----------------------|--------|
| Industry Standard(s) | cCSAus |
|----------------------|--------|

Logistics

| | |
|-----------------|---|
| Carton Quantity | 5 |
|-----------------|---|

Product Assets

- [Catalog Page - WDK K-19 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Engineering Drawing - GFP3305 AutoCAD Drawing](#)
- [Engineering Drawing - M9094_ACAD](#)

Installation Manuals - WIRING_PD1978_INSTALLINST
Literature - PULP & PAPER SOLUTIONS
Literature - Pulp & Paper Solutions
Sales Drawings - WDK_GFP3305_DRAWING_PDF

Sales Drawings - M9094
Specifications - GFP3305
Warranty - Industrial & Commercial Products



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved
WDK-GFP3305-SPEC-EN | REV 3/2025