



# GFPIL30125LKM

By Hubbell Wiring Device-Kellems  
 Catalog # [GFPIL30125LKM](#)



Power Protection Products, GFCI Linecords, Commercial, Manual Set, 30A 125V, L5-30R, 25' Cord Length, Triple Tap, Yellow.

## Features

- Electromagnetic Latching Mechanism
- Trips if ground and neutral touch at load side
- Red blinking light plus optional audible alarm
- Open neutral protection Trips upon loss of neutral

## Application

Line Cord with Devices

## General

Color	Yellow
Construction	Fabricated
EU RoHS Indicator	No
Item Type	Industrial Grade
Material - Insulation	Elastomer
Material - Jacket	PVC
OEM Brand Name	Hubbell Wiring Device-Kellems
Performance	<ul style="list-style-type: none"> <li>• Electrical - Dielectric Withstand - 1500 VRMS across contact, 4000 VRMS between conductors &amp; enclosure</li> <li>• Electrical - Operating Voltage Range - 85% to 110%</li> <li>• Electrical - Rated Voltage - 120V AC, 240V AC, 120/240V AC, 3Ø 250V AC, 3Ø 120/208V AC</li> <li>• Electrical - Surge Withstand - 6000V impulse, 0.5 ms rise time 100kHz ringing frequency</li> <li>• Environmental - Construction - Industrial grade design</li> <li>• Environmental - Housing Rating - UL Type 4X</li> <li>• Environmental - Leakage Current - At 93% Humidity leakage current is zero</li> <li>• Environmental - Operating Temperature - -35°C to 66°C, -30°F to 150°F.</li> <li>• Environmental - Type -</li> </ul>

## Dimensions

Outside Diameter	0.335
Weight	2.25 lb

## Electrical Ratings

Amperage Rating	30 A
Connectivity	Plug-In
Current / Amperage Rating	30 A
Current Rating	30 A
Voltage Rating	120 VAC
Voltage Rating Description	120 VAC

## Conductor Related

Conductor Size	#10 AWG
Conductor Type	Copper
Number Of Conductors	3
Strands	Multi

## Certifications and Compliance

Industry Standard(s)	UL Listed
Nema Rating	L5-30

## Product Assets

- [Catalog Page - Wiring L-20 Catalog page](#)
- [Catalogs - Wiring Full Catalog](#)
- [Engineering Drawing - GFPIL30125LKM AutoCAD Drawing](#)
- [Installation Manuals - WIRING\\_PD2165\\_INSTALLINST](#)
- [Literature - WIRING\\_WLFVM034](#)
- [Literature - Pulp & Paper Solutions](#)
- [Sales Drawings - WDK\\_GFPIL30125LK\\_DRAWING\\_PDF](#)
- [Warranty - Industrial & Commercial Products](#)

## Related Products

- [GFPIL30250LKM - Circuit Guard® Extra Heavy Duty Portable Locking GFCI with Manual Set, 30A, 240V AC, 2', Yellow](#)
- [GFPIL30250LKA - Circuit Guard® Extra Heavy Duty Portable Locking GFCI with Automatic Set, 30A, 240V AC, 2', Yellow](#)
- [GFPIL30125LKA - Circuit Guard® Extra Heavy Duty Portable Locking GFCI with Automatic Set, 30A, 120V AC, 2', Yellow](#)

Environmental Type

Meets UL943 Class A GFCI

Series	Extra Heavy Duty
Style	Manual Set
Temperature Rating	-35 Degrees C to 66 Degrees C (-30 Degrees F to 150 Degrees F)
Type	Portable, Locking
UPC	783585692159



**A proud member of the Hubbell Family.**

©2023 Hubbell Incorporated. All rights reserved.  
WDK-GFPIL30125LKM-SPEC-EN | REV 5/2023