



GFPIL30250LKM

By Hubbell Wiring Device-Kellems
Catalog # [GFPIL30250LKM](#)

Power Protection Products, GFCI Linecords, Commercial, Manual Set, 30A 250V, L6-20R, 25' Cord Length, Triple Tap, Yellow.



Features

- Electromagnetic Latching Mechanism
- Trips if ground and neutral touch at load side
- Red blinking light plus optional audible alarm
- Open neutral protection Trips upon loss of neutral

Application

Line Cord with Devices

General

Color	Yellow
Construction	Fabricated
EU RoHS Indicator	No
Item Type	Industrial Grade
Material - Insulation	Elastomer
Material - Jacket	PVC
OEM Brand Name	Hubbell Wiring Device-Kellems
Performance	<ul style="list-style-type: none"> • Electrical - Dielectric Withstand - 1500 VRMS across contact, 4000 VRMS between conductors & enclosure • Electrical - Operating Voltage Range - 85% to 110% • Electrical - Rated Voltage - 120V AC, 240V AC, 120/240V AC, 3Ø 250V AC, 3Ø 120/208V AC • Electrical - Surge Withstand - 6000V impulse, 0.5 ms rise time 100kHz ringing frequency • Environmental - Construction - Industrial grade design • Environmental - Housing Rating - UL Type 4X • Environmental - Leakage Current - At 93% Humidity leakage current is zero • Environmental - Operating Temperature - -35°C to 66°C, -30°F to 150°F. • Environmental - Type -

Dimensions

Outside Diameter	0.335
Weight	2.25 lb

Electrical Ratings

Amperage Rating	30 A
Connectivity	Plug-In
Current / Amperage Rating	30 A
Current Rating	30 A
Voltage Rating	250 VAC
Voltage Rating Description	250 VAC

Conductor Related

Conductor Size	#10 AWG
Conductor Type	Copper
Number Of Conductors	3
Strands	Multi

Certifications and Compliance

Industry Standard(s)	UL Listed
Nema Rating	L6-30

Product Assets

[Catalog Page - Wiring L-20 Catalog page](#)
[Catalogs - Wiring Full Catalog](#)
[Engineering Drawing - GFPIL30250LKM AutoCAD Drawing](#)
[Installation Manuals - WIRING_PD2165_INSTALLINST](#)
[Literature - WIRING_WLFVM034](#)
[Literature - Pulp & Paper Solutions](#)
[Sales Drawings - WDK_GFPIL30250LK_DRAWING_PDF](#)
[Warranty - Industrial & Commercial Products](#)

Related Products

[GFPIL30125LKM - Circuit Guard® Extra Heavy Duty Portable Locking GFCI with Manual Set, 30A, 120V AC, 2', Yellow](#)
[GFPIL30125LKA - Circuit Guard® Extra Heavy Duty Portable Locking GFCI with Automatic Set, 30A, 120V AC, 2', Yellow](#)
[GFPIL30250LKA - Circuit Guard® Extra Heavy Duty Portable Locking GFCI with Automatic Set, 30A, 240V AC, 2', Yellow](#)

Environmental Type
Meets UL943 Class A GFCI

Series	Extra Heavy Duty
Style	Manual Set
Temperature Rating	-35 Degrees C to 66 Degrees C (-30 Degrees F to 150 Degrees F)
Type	Portable, Locking
UPC	783585692173



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
WDK-GFPIL30250LKM-SPEC-EN | REV 5/2023