



Triple Tap Outlet Portable GFCI Line Cord, Automatic Set, 15A, 120V AC, 2' - 12/3 SJEOW

By Hubbell Wiring Device-Kellems
Catalog # [GFPST2TTA](#)

Circuit Guard® Heavy Duty Triple Tap Outlet Portable GFCI Line Cord, Automatic Set, 15A, 120V AC, 2' - 12/3 SJEOW



*Representative Image

Features

- High impact UV stabilized housing for long life
- All-glass circuit board provides moisture immunity
- Watertight GFCI housing for use in harsh environments
- Open neutral protection Trips upon loss of neutral
- Self-test functionality in accordance with UL 943

Application

Outdoor/Indoor

General

Color	Black/Yellow
Environmental Conditions	NEMA 3R
Material	Polycarbonate
Number Of Poles	2
Series	GFCI
Style	Triple Tap Outlet
Temperature Rating	-30°F (-35°C) - 150°F (66°C)
Type	Portable GFCI
UPC	783585694276

Electrical Ratings

Amperage Rating	15 A
Phase	Single
Voltage Rating	120 V
Wattage	1800 W

Conductor Related

Number Of Wires 3

Certifications and Compliance

Industry Standard(s) cULus 943
Nema Rating 5-15

Product Assets

[Installation Manuals - PD3067](#)
[Sales Drawings - M14730](#)
[Warranty - Industrial & Commercial Products](#)

Related Products

[GFPST25CA - Single Outlet Portable GFCI Line Cord, Automatic Set, 15A, 120V AC, 25' - 12/3 SJEOW](#)
[GFPST515A - Portable GFCI Plug, Automatic Set, 15A, Black](#)
[GFPST15LA - Portable GFCI Plug, Automatic Set, 15A, 120V AC, 15' with flying leads - 14/3 SJEOW](#)
[GFPST15LM - Portable GFCI Plug, Manual Set, 15A, 120V AC, 15' with flying leads - 14/3 SJEOW](#)
[GFPST25CM - Single Outlet Portable GFCI Line Cord, Manual Set, 15A, 120V AC, 25' - 12/3 SJEOW](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK-GFPST2TTA-SPEC-EN | REV 2/2024