

Power Protection Devices,
Receptacle, Self Test, GFCI, TR,
Commercial Grade, 20A 125V, 2-
Pole 3-Wire Grounding, 5- 20R,
Gray

By Hubbell Wiring Device-Kellems
Catalog # [GFRTR20GRY](#)



Power Protection Devices, Receptacle, Self Test, GFCI, TR,
Commercial Grade, 20A 125V, 2-Pole 3-Wire Grounding, 5- 20R,
Gray.

General

Catalog Number	GFRTR20GRY
Color	Gray
EU RoHS Indicator	Contact Manufacturer
Series	Heavy Duty
Specifications	<ul style="list-style-type: none">• Base - Nylon• Face - Nylon• Ground Contacts - Brass• Mounting Screws - Zinc plated steel• Mounting Strap - Zinc plated steel• Power Contacts - Brass
Style	Standard
Type	Tamper-Resistant
UPC	883778999659

Electrical Ratings

Current / Amperage Rating	20 A
---------------------------	------

Voltage Rating Description	125 V
----------------------------	-------

Certifications And Compliance

Industry Standard(s)	Meets All NEC® Requirements
Nema Rating	5-20R

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog Page - WDK K-4 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Engineering Drawing - M-14627 AutoCAD Drawing](#)
- [Installation Manuals - PD2987](#)
- [Literature - Commercial GFCI Receptacles](#)
- [Literature - FREQUENTLY ASKED QUESTIONS Commercial GFCI Receptacles](#)
- [Sales Drawings - M14627](#)
- [Specifications - WIRING_GFRTR20GRY_spec](#)