

Extra Heavy Duty Industrial Tamper-Resistant/Weather Resistant AUTOGUARD® Self-Test GFCI Receptacle, 15A, Ivory

By Hubbell Wiring Device-Kellems
Catalog # [GFSG5262I](#)

AUTOGUARD® Self-Test Tamper-Resistant Weather-Resistant
GFCI 15A Receptacle, 125V Industrial Grade Extra Heavy Duty,
Back and Side Wired.



Features

Patented auto monitor

General

Application	Industrial Grade
Catalog Number	GFSG5262I
Color	Ivory
Item Type	Style Line GFCI Receptacle
Material	PC/PBT
Series	Extra Heavy Duty
Size	4.06 in x 1.75 in x 1.48 in
Type	Tamper-Resistant/Weather-Resistant
	Tamper-Resistant/Weather-Resistant
UPC	783585745909

Dimensions

Dimensions	1.48 in x 1.75 in x 4.06 in
Height	4.06 in
Length	1.48 in
Width	1.75 in

Electrical Ratings

Current / Amperage Rating	15 A
Phase	Single Phase
Voltage Rating	125 VAC
Wattage	1875 W

Conductor Related

Wire Size	#14 - #10 AWG
-----------	---------------

Certifications And Compliance

Industry Standard(s)	UL 943 and Meets All NEC® Requirements
Nema Rating	5-15R

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog Page - WDK K-3 Catalog Page](#)
- [Catalog Page - WDK AA-42 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Installation Manuals - PD2987](#)
- [Literature - Extra Heavy Duty Industrial GFCI Receptacles](#)
- [Sales Drawings - M14626](#)
- [Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WDK-GFSG5262I-SPEC-EN | REV 6/2024