

# Extra Heavy Duty Industrial Tamper-Resistant/Weather Resistant AUTOGUARD® Self-Test GFCI Receptacle, 15A, White

By Hubbell Wiring Device-Kellems  
Catalog # [GFSG5262W](#)

AUTOGUARD® Self-Test Tamper-Resistant Weather-Resistant  
GFCI 15A Receptacle, 125V Industrial Grade Extra Heavy Duty,  
Back and Side Wired.



## Features

Patented auto monitor

## General

Application	Industrial Grade
Catalog Number	GFSG5262W
Color	White
Item Type	Style Line GFCI Receptacle
Material	PC/PBT
Series	Extra Heavy Duty
Size	4.06 in x 1.75 in x 1.48 in
Type	Tamper-Resistant/Weather-Resistant
	Tamper-Resistant/Weather-Resistant
UPC	783585745923

## Dimensions

Dimensions	1.48 in x 1.75 in x 4.06 in
Height	4.06 in
Length	1.48 in
Width	1.75 in

## Electrical Ratings

Current / Amperage Rating	15 A
Phase	Single Phase
Voltage Rating	125 VAC
Wattage	1875 W

## Conductor Related

Wire Size	#14 - #10 AWG
-----------	---------------

## Certifications And Compliance

Industry Standard(s)	UL 943 and Meets All NEC® Requirements
Nema Rating	5-15R

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

- [Catalog Page - WDK K-3 Catalog Page](#)
- [Catalog Page - WDK AA-42 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Installation Manuals - PD2987](#)
- [Literature - Extra Heavy Duty Industrial GFCI Receptacles](#)
- [Sales Drawings - M14626](#)
- [Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
WDK-GFSG5262W-SPEC-EN | REV 6/2024