

# Extra Heavy Duty Industrial Tamper-Resistant/Weather Resistant AUTOGUARD® Self-Test GFCI Receptacle, 20A, Red

By Hubbell Wiring Device-Kellems  
Catalog # [GFSG5362R](#)

20A, 125V Industrial Grade, Tamper-Resistant, Weather-Resistant, Ground Fault Receptacle.



## Features

- Heavy duty robust construction, high impact resistant polyester housing
- Corrosion Resistant: nickel-plated face contacts, mounting strap, line/load terminals and terminal clamps, stainless steel screws
- Patented auto monitor, power denial technology

## General

Application	Industrial Grade
Catalog Number	GFSG5362R
Color	Red
Item Type	Style Line GFCI Receptacle
Material	PC/PBT
Series	Extra Heavy Duty
Size	4.06 in x 1.75 in x 1.48 in
Type	Tamper-Resistant/Weather-Resistant Tamper-Resistant/Weather-Resistant
UPC	783585745978

## Dimensions

Dimensions	1.48 in x 1.75 in x 4.06 in
Height	4.06 in
Length	1.48 in
Width	1.75 in

## Electrical Ratings

Current / Amperage Rating	20 A
Phase	Single Phase
Voltage Rating	125 VAC
Wattage	2500 W

## Conductor Related

Wire Size	#14 - #10 AWG
-----------	---------------

## Certifications And Compliance

Industry Standard(s)	UL 943 and Meets All NEC® Requirements
Nema Rating	5-20R

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalog Page - WDK K-3 Catalog Page](#)  
[Catalogs - WDK Catalog Full 2024](#)  
[Installation Manuals - PD2987](#)  
[Literature - Extra Heavy Duty Industrial GFCI Receptacles](#)  
[Sales Drawings - M14626](#)  
[Warranty - Industrial & Commercial Products](#)



**A Hubbell brand**

©2024 Hubbell Incorporated. All rights reserved  
WDK-GFSG5362R-SPEC-EN | REV 6/2024