



Switches and Lighting Control, Occupancy Sensor, FS Adapter Plate for AHP1600 Series, Cast Aluminum

By Hubbell Wiring Device-Kellems
Catalog # [HAP1](#)



Switches and Lighting Control, Occupancy Sensor, FS Adapter Plate for AHP1600 Series, Cast Aluminum

General

Color	Gray
Operating Temperature	-40°F to 149°F (-40°C to 65°C)
Series	Wall Mount
Type	Accessories
UPC	783585256139

Electrical Ratings

Voltage Rating	24 VDC
Voltage Rating Description	24V DC

Certifications and Compliance

Nema Rating	NEMA 4X
-------------	---------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - Wiring E-13 Catalog Page](#)
[Catalogs - Wiring Full Catalog](#)
[Literature - MAXX™ Harsh Environment & OPTIMYZER® Watertight Sensors](#)
[Sales Drawings - WDK_HAP1_DRAWING_PDF](#)
[Warranty - HMOSS Occupancy Motion Sensors](#)

Related Products

[HAP2 - Switches and Lighting Control, Occupancy Sensor, Hub Cover, 1/2" X 1", Includes Mounting Screws and Gasket](#)
[HAP4 - Switches and Lighting Control, Occupancy Sensor, Hub Cover for AHP1600 Series, 1/2"](#)
[ACIPE - Switches and Lighting Controls, Protective Enclosure for IR Ceiling Sensor, NEMA 4X](#)
[AHP1500CRP - Switches and Lighting Control, HarshEnvironment, Occupancy Sensors, Passive Infrared, Ceiling Mount, 1500Square Feet, Photocell and Relay](#)
[CU300HD - Switches and Lighting Control, Occupancy Sensor, Control Unit, 120/277V AC, Heavy Duty Relay, Latching](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
WDK-HAP1-SPEC-EN | REV 5/2023