

Kellems Wire Managent, Cord
Connector, Non-Metallic, .37-.50",
3/4", Gray

By Hubbell Wiring Device-Kellems
Catalog # [HBL10CM35S](#)

Kellems® Cord Connector, Non-Metallic, .37-.50", ¾"



General

Application	Straight Male
Catalog Number	HBL10CM35S
Color	Gray
EU RoHS Indicator	Yes
Environmental Conditions	Suitable For Use In Wet Locations When Used With A Listed Nylon Washer Between Box And Fitting.
Item Type	Cord Connectors
Material	Nylon
Material - Mounting Hardware	Locknut or Tapped Opening
OEM Brand Name	Hubbell Wiring Device-Kellems
Temperature Rating	Minimum -30 Deg F to 225 Deg F (-43 Deg C to 107 Deg C)
UPC	783585808031

Dimensions

Display Size	3/4" NPT
--------------	----------

Conductor Related

Conductor Range	0.38-0.5 in (9.5-12.7 mm)
Number of Conductors	Single

Certifications And Compliance

Standards - RoHS Compliance	CM
Status	

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog Page - WDK AA-51 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Literature - Hubbell Marine Full Line Catalog](#)
- [Literature - FOOD & BEVERAGE SOLUTIONS](#)
- [Literature - FOOD & BEVERAGE SOLUTIONS](#)
- [Literature - Pulp & Paper Solutions](#)
- [Literature - PULP & PAPER SOLUTIONS](#)
- [Warranty - Industrial & Commercial Products](#)



A Hubbell brand