



Surge Protective Devices, Plug-In, 1) Receptacle and 1) CATV, 15A 125V , 750 Joules, Ivory

By Hubbell Wiring Device-Kellems
Catalog # [HBL1PI750C](#)



Surge Protective Devices, Plug-In, 1) Receptacle and 1) CATV,
15A 125V , 750 Joules, Ivory

Application

F-Coax Connectors

General

| | |
|------------------------------|--|
| EU RoHS Indicator | No |
| Environmental Conditions | Indoor Dry Unless Protected By Additional Means |
| Indicator(s) Type | LED Indicator |
| Item Type | Surge Protection Plug Strips |
| Material | Non-Metallic |
| Material - Mounting Hardware | Portable |
| OEM Brand Name | Hubbell Wiring Device- Kellems |
| Operating Temperature | 32 Deg F to 140 Deg F (0 Deg C to 60 Deg C) |
| Outlet | Straight Blade 5-15R |
| Response Time | 5 |
| UPC | 783585120959 |

Dimensions

Display Size 750 Joules

Electrical Ratings

| | |
|---------------------------|--------------|
| Amperage Rating | 15 A |
| Connectivity | Plug-In |
| Current / Amperage Rating | 15 A |
| Current Rating | 15 A |
| Frequency Rating | 60 Hz |
| Phase | Single Phase |
| Voltage Rating | 125 VAC |

Product Assets

[Installation Manuals - WIRING_PD2424_INSTALLINST](#)
[Sales Drawings - WDK_HBL1PI750C_DRAWING_PDF](#)
[Warranty - Surge Plug Strips](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
WDK-HBL1PI750C-SPEC-EN | REV 5/2023