



**Surge Protective Devices, Plug-In,
1) Receptacle and 1)
Telephone/Fax, 15A 125V, 750
Joules, Ivory**

By Hubbell Wiring Device-Kellems
Catalog # [HBL1PI750M](#)



Surge Protective Devices, Plug-In, 1) Receptacle and 1)
Telephone/Fax, 15A 125V, 750 Joules, Ivory

General

EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Indicator(s) Type	LED Indicator
Item Type	Surge Protection Plug Strips
Material	Non-Metallic
Material - Mounting Hardware	Portable
OEM Brand Name	Hubbell Wiring Device- Kellems
Operating Temperature	32 Deg F to 140 Deg F (0 Deg C to 60 Deg C)
Outlet	Straight Blade 5-15R
Response Time	5
UPC	783585120942

Dimensions

Display Size	750 Joules
--------------	------------

Electrical Ratings

Amperage Rating	15 A
Connectivity	Plug-In
Current / Amperage Rating	15 A
Current Rating	15 A
Frequency Rating	60 Hz
Phase	Single Phase
Voltage Rating	125 VAC

Product Assets

[Installation Manuals - WIRING_PD2424_INSTALLINST](#)
[Sales Drawings - WDK_HBL1PI750M_DRAWING_PDF](#)
[Warranty - Surge Plug Strips](#)



A proud member of the Hubbell Family.