

Locking Devices, Twist-Lock®,
Watertight Safety Shroud, Male
Plug, 20A 250V, 2-Pole 3-Wire
Grounding, L6-20P, Screw Terminal,
Black and White

By Hubbell Wiring Device-Kellems
Catalog # [HBL2321SW](#)

Locking Devices, Twist-Lock®, Watertight Safety-Shroud®, Male Plug, 20A 250V AC, 2-Pole 3-Wire Grounding, NEMA L6-20P, Screw Terminal, Black PBT housing, White PBT clamps.

Features

- UL Type 4X Environmental seal protects connection while in use.
- Impact resistant shroud protects blades against bending and breaking.
- Reduces exposure to arcing when connecting or disconnecting under load.
- Superior cord grip design protects terminations from excess strain.

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - V0 per UL94 or CSA 22.2 No.0.17
- Environmental - Moisture Resistance - Type 4, 4X, 12, IP66 suitability
- Environmental - Operating Temperatures - Maximum Continuous 75°C Minimum -40°C (w/o impact)
- Mechanical - Terminal Accommodation - #16 AWG - #8 AWG stranded copper wire only.
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498

General

Catalog Number	HBL2321SW
Color	Black, White
Cord Range	0.360"-0.930" (9-24)
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Watertight
Item Type	20A Watertight Safety-Shroud® Plug
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Wiring Device-Kellems



Operating Temperature

Specifications

Type
UPC

Dimensions

Dimensions
Display Size
Height
Length
Weight
Width

Electrical Ratings

Amperage Rating
Connectivity
Current / Amperage Rating
Current Rating
Dielectric Strength
Phase
Voltage Rating
Voltage Rating Description

Conductor Related

Maximum continuous 75°C and minimum -40°C without Impact

- Assembly Screws - Stainless Steel
- Blades - Brass
- Closure Plug - Santoprene
- Housing / Cord Clamp - PBT
- Terminal Clamp - Cold rolled steel – nickel plated
- Terminal Retainer - Clear polycarbonate
- Terminal Screws - #10-32 Brass (Phillips / Slotted / Robertson)
- Watertight Gland - Neoprene

Plugs
783585231105

2.77 in x 2.77 in x 4.40 in
Standard Sized
4.4 in
2.77 in
0.6 lb
2.77 in

20 A
Pressure Terminal Screws
20 A
20 A
Withstands 2,000V minimum
Single Phase
250 V
250 V

Cable Range	0.360 - 0.930 in
Cord Type	All Listed Portables
Number Of Wires	3-Wire
Wire Size	#16 AWG to #8 AWG

Certifications And Compliance

Buy America(n) Qualified	Buy American Act Compliant (All status valid till December 2024)
Industry Standard(s)	UL Listed, CSA Certified To Type 4, 4X And Type 12
Nema Rating	L6-20P
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	10
Pallet Quantity	960

Product Assets

[Brochures - Circuit-Lock® Motor Disconnects](#)
[Catalog Page - WDK C-3 Catalog Page](#)

[Catalog Page - WDK B-41 Catalog Page](#)
[Catalog Page - WDK B-20 Catalog Page](#)
[Catalogs - WDK Catalog Full 2024](#)
[Engineering Drawing - HBL2321SW AutoCAD Drawing](#)
[Installation Manuals - WIRING_PD1270_INSTALLINST](#)
[Literature - Education Application Guide](#)
[Literature - Food Processing Guide](#)
[Literature - PULP & PAPER SOLUTIONS](#)
[Literature - Pulp & Paper Solutions](#)
[Literature - Industrial Solutions](#)
[Literature - Safety Product Guide](#)
[Literature - Circuit-Lock® Rounded Sloped Top Motor Disconnects](#)
[Literature - Healthcare Application Guide](#)
[Literature - Wiring Device Solutions for Strategic Manufacturing Facilities](#)
[Literature - Entertainment Product Solution Guide](#)
[Sales Drawings - WDK_HBL2321SW_DRAWINGS_PDF](#)
[Specifications - Wiring HBL2321SW Specification Sheet](#)
[Warranty - Industrial & Commercial Products](#)
[Video - Circuit-Lock® Rounded Sloped Top Motor Disconnects](#)
[Video - Insulgrip Twist-Lock and Straight Blade Devices](#)
[Video - Twist-Lock Devices](#)

