

Locking Devices, Twist-Lock®,
Watertight Safety Shroud,
Receptacle 20A 3-Phase Delta 250V
AC, 3-Pole 4-Wire Grounding, L15-
20R, Screw Terminal, Gray

By Hubbell Wiring Device-Kellems
Catalog # [HBL2420SW](#)

Locking Devices, Twist-Lock®, Watertight Safety-Shroud®,
Receptacle 20A 3-Phase Delta 250V AC, 3-Pole 4-Wire
Grounding, NEMA L15-20R, Screw Terminal, PBT housing and
flange, Gray.

Application

Heavy Duty Industrial Shrouded Watertight

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - V2 or better per UL94/CSA 22.2 No.0.17
- Environmental - Moisture Resistance - IP20 Suitability
- Environmental - Operating Temperatures - Maximum Continuous 75°C, Minimum -40°C (w/o impact)
- Mechanical - Terminal Accommodation - #16 AWG - #8 AWG solid or stranded copper wire only.
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498

General

Catalog Number	HBL2420SW
EU RoHS Indicator	Yes
Environmental Conditions	Watertight
Horsepower - Maximum	3
Item Type	Receptacles
Material	Thermoplastic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3-Pole
OEM Brand Name	Hubbell Wiring Device-Kellems
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Specifications	- Body Contact Carrier - Natural (white) nylon - Contacts - Brass - Drive Screws - Steel, zinc plated - Housing / Cover - Gray RPT - Lift-Cover Spring & Pin - Stainless Steel



Type
UPC

- Terminal Retainer - Clear polycarbonate
- Receptacle
783585231341

Dimensions

Dimensions	3.75 in x 3.75 in x 2.90 in
Display Size	Standard Sized Product
Height	2.9 in
Length	3.75 in
Weight	0.6 lb
Width	3.75 in

Electrical Ratings

Amperage Rating	20 A
Connectivity	Back Wired Screw Terminals
Current / Amperage Rating	20 A
Current Rating	20 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Three Phase
Voltage Rating	250 V
Voltage Rating Description	3 Phase 250 VAC

Conductor Related

Number Of Wires	4-Wire
Wire Size	#16 AWG to #8 AWG

Certifications And Compliance

Industry Standard(s)	UL Listed, CSA Certified To Type 4, 4X And Type 12
Nema Rating	L15-20R

Logistics

Carton Quantity	5
Pallet Quantity	1000

Product Assets

[Brochures - Circuit-Lock® Motor Disconnects](#)

[Catalog Page - WDK C-3 Catalog Page](#)

[Catalog Page - WDK B-23 Catalog Page](#)

[Catalog Page - WDK B-41 Catalog Page](#)

[Catalogs - WDK Catalog Full 2024](#)

[Engineering Drawing - HBL2420SW AutoCAD Drawing](#)

[Installation Manuals - WIRING_PD1267_INSTALLINST](#)

[Literature - Safety Product Guide](#)

[Literature - Education Application Guide](#)

[Literature - Food Processing Guide](#)

[Literature - Circuit-Lock® Rounded Sloped Top Motor Disconnects](#)

[Literature - PULP & PAPER SOLUTIONS](#)

[Literature - Pulp & Paper Solutions](#)

[Literature - Wiring Device Solutions for Strategic Manufacturing Facilities](#)

[Literature - Entertainment Product Solution Guide](#)

[Sales Drawings - WDK_HBL2420SW_DRAWINGS_PDF](#)

[Specifications - Wiring HBL2420SW Specification Sheet](#)

[Warranty - Industrial & Commercial Products](#)

[Video - Circuit-Lock® Rounded Sloped Top Motor Disconnects](#)

[Video - Insulgrip Twist-Lock and Straight Blade Devices](#)

[Video - Twist-Lock Devices](#)



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved
WDK-HBL2420SW-SPEC-EN | REV 7/2025