

Watertight Devices, Twist-Lock®
Plug, 15A, 125V AC, 2 Pole, 3 Wire,
Thermoplastic elastomer, NEMA L5-
15P, Yellow

By Hubbell Wiring Device-Kellems
Catalog # [HBL24W47A](#)

Watertight Devices, Twist-Lock® Plug, 15A, 125V AC, 2 Pole, 3
Wire, Thermoplastic elastomer, NEMA L5-15P, Yellow

Features

- Smooth body design minimizes collection points simplifying the wash down process
- Strain relief nut always seals on the body, minimizing debris collection
- Stainless steel hardware and corrosion-resistant connection points

Performance

- Electrical - Current Interrupting - Rated for current interruption per UL498
- Electrical - Dielectric Voltage - 2500V AC
- Electrical - Max Working Voltage - As marked
- Electrical - Temperature Rise - 30°C max per UL498 at rated current
- Environmental - UV resistance - All exposed materials are UV stabilized
- Environmental - Moisture Resistance - UL Listed 4, 4X, 12, 6, 6P
- Environmental - Operating Temperatures - -40°C (without impact) to +60°C continuous
- Mechanical - Cord Accommodation - 0.375"-0.625" (9.5-15.9)

General

Catalog Number	HBL24W47A
Color	Yellow
EU RoHS Indicator	Contact Manufacturer
Item Type	15A Watertight Twist-Lock® Plug
Number Of Poles	2-Pole
Type	Plugs
UPC	783585131245

Dimensions

Dimensions	1.85 in x 1.85 in x 3.21 in
Height	3.21 in
Length	1.85 in
Width	1.85 in

Electrical Ratings

Amperage Rating	15 A
Current / Amperage Rating	15 A
Voltage Rating	125 V
Voltage Rating Description	125 V

Conductor Related

Number Of Wires	3-Wire
Wire Size	16/3 SJ to 10/3 SJ, 18/3 S to 12/3 S

Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
Industry Standard(s)	Meets NEMA WD-1, WD-6 And ANSI Standards
Nema Rating	L5-15P
Standards - RoHS Compliance	CM
Status	

Logistics

Carton Quantity	25
Pallet Quantity	1800

Product Assets

- [Catalog Page - WDK C-6 Catalog Page](#)
- [Catalog Page - WDK C-7 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Engineering Drawing - HBL24W47A AutoCAD Drawing](#)
- [Installation Manuals - WIRING_PD2634_INSTALLINST](#)
- [Literature - Food Processing Guide](#)
- [Literature - PULP & PAPER SOLUTIONS](#)
- [Literature - Pulp & Paper Solutions](#)
- [Literature - Watertight Wiring Devices](#)
- [Literature - Wiring Device Solutions for Strategic Manufacturing Facilities](#)
- [Literature - Entertainment Product Solution Guide](#)
- [Literature - Emergency Preparedness for Healthcare](#)
- [Sales Drawings - M-12623](#)
- [Specifications - Wiring HBL24W47A Specification Sheet](#)
- [Warranty - Industrial & Commercial Products](#)





A Hubbell brand