

Surge Protective Devices, Plug-In,
3) Receptacles, 15A 125V, 2-Pole 3-
Wire Grounding, 5-15R, 750 Joules,
Ivory

By Hubbell Wiring Device-Kellems
Catalog # [HBL3PI750](#)

Surge Protective Devices, Plug-In, 3) Receptacles, 15A 125V, 2-
Pole 3- Wire Grounding, 5-15R, 750 Joules, Ivory

Features

- Plug-In
- 3) Receptacles
- 15A 125V
- 2-Pole 3- Wire Grounding

Application

Standard Devices and Cord Holder

General

Catalog Number	HBL3PI750
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Indicator(s) Type	LED Indicator
Item Type	Surge Protection Plug Strips
Material	Non-Metallic
Material - Mounting Hardware	Portable
OEM Brand Name	Hubbell Wiring Device-Kellems
Operating Temperature	32 Deg F to 140 Deg F (0 Deg C to 60 Deg C)
Outlet	Straight Blade 5-15R
Response Time	5



Specifications

- Joule Rating - 750
 - No.of Outlets - 3
 - Peak AMP Rating - 13.5kA
- UPC
783585120966

Dimensions

Display Size
750 Joules

Electrical Ratings

Amperage Rating	15 A
Connectivity	Plug-In
Current / Amperage Rating	15 A
Current Rating	15 A
Frequency Rating	60 Hz
Phase	Single Phase
Voltage Rating	125 VAC

Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Engineering Drawing - HBL3PI750 AutoCAD Drawing](#)
- [Installation Manuals - WIRING_PD2424_INSTALLINST](#)
- [Sales Drawings - WDK_HBL3PI750_DRAWING_PDF](#)
- [Specifications - HBL3PI750](#)
- [Warranty - Surge Plug Strips](#)