



4-PLEX, Hospital Grade Surge Suppression Receptacle, 20A 125V, 5-20R, with Surge, Ivory

By Hubbell Wiring Device-Kellems
Catalog # [HBL420HIS](#)

4-PLEX, Hospital Grade Surge Suppression Receptacle, 20A 125V, 5-20R, with Surge, Ivory



Features

- Mounts directly to 4-inch square box
- Heavy duty, impact resistant housing
- Removable knockouts for mounting
- Heavy duty, triple wipe, brass power and ground contacts

Application

4-Plex with LED

General

Color	Ivory
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Indicator(s) Type	LED Only
Item Type	Surge Protection Receptacles
Material	Composite
Material - Mounting Hardware	Mounting Screws
OEM Brand Name	Hubbell Wiring Device-Kellems
Operating Temperature	32 Deg F to 140 Deg F (0 Deg C to 60 Deg C)
Outlet	Straight Blade
Performance	<ul style="list-style-type: none"> • Electrical - Frequency - 60Hz • Electrical - Protection Modes - Normal and Common Modes • Electrical - Response Time - Approximately 5 ns • Electrical - Transient Suppression - Peak Energy (10 X 100 μs), Peak Current (8 X 20 μs) • Electrical - Voltage - 20V AC + 10% - 15% • Environmental - Flammability - UL 94V-2 • Environmental - Operating Temperature - -40°F to 140°F (-40°C to 60°C)
Response Time	5
Series	Hospital Grade
Type	4-Plex
UPC	783585017907

Electrical Ratings

Amperage Rating	20 A
Connectivity	Terminal Screws
Current / Amperage Rating	20 A
Current Rating	20 A
Frequency Rating	60 Hz
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • Certified to CSA 22.2, No. 42 File 285 • Listed to UL Standard 498 File E2186
Nema Rating	5-20R

Logistics

Carton Quantity	5
-----------------	---

Product Assets

[Catalog Page - Wiring N-13 Catalog page](#)
[Catalog Page - Wiring A-28 Catalog page](#)
[Catalog Page - Wiring M10 Catalog page](#)
[Catalogs - Wiring Full Catalog](#)
[Engineering Drawing - HBL420HIS AutoCAD Drawing](#)
[Installation Manuals - WIRING_B04578H02_INSTALLINST](#)
[Literature - WLBD026_Duct Products Brochure_WEB](#)
[Literature - SpikeShield® Power Quality Surge Protective Devices](#)
[Sales Drawings - WDK_HBL420_DRAWING_PDF](#)
[Warranty - Industrial & Commercial Products](#)

Related Products

[HBL415I - Straight Blade Devices, Receptacles, 4- Plex, Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, 15A 125V, 5- 15R, Ivory, Single Pack](#)
[HBL420IS - Surge Protective Devices, 4-PLEX, Surge Suppression Receptacle, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, Ivory.](#)
[HBL415IS - 4-PLEX Surge Suppression Receptacle, 2Pole 3Wire, 15A 125V, 5-15R, Ivory.](#)
[HBL420HI - Straight Blade Devices, Receptacles, 4- Plex, Hospital Grade, 2-Pole 3-Wire Grounding, 20A 125V, 5-20R, Ivory, Single Pack](#)
[HBL4API - Straight Blade Devices, Accessories, 4-Plex Adapter Plate for 1 and 2 Gang device boxes. Ivory. Single Pack](#)

Dimensions

Display Size

Standard



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
WDK-HBL420HIS-SPEC-EN | REV 5/2023