

PS, IEC, INLT, 3P4W, 60A 380-415V, VO

By Hubbell Wiring Device-Kellems  
Catalog # [HBL460B6V02](#)

PS, IEC, INLT, 3P4W, 60A 380-415V, VO

Features

- Solid one-piece pins for reliable electrical contact
- Gasketed sealing ring provides watertight seal
- Raised collar surrounds each phase pin

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstand 3000V AC
- Electrical - Max. Working Voltage - 600V RMS
- Environmental - Flammability - HB or better per UL 94 or CSA C22.2 No. 0.17
- Environmental - Ingress Protection - IP67 Suitability
- Environmental - Moisture Resistance - Watertight per IEC 60309-1
- Environmental - Operating Temperatures - Maximum Continuous 75°C
- Minimum - 40°C w/o impact
- Mechanical - Impact Resistance - Per CSA C22.2 No. 182.1 / UL1682
- Mechanical - Product Identification - Ratings are a permanent part of the device housing
- Mechanical - Terminal Identification - Terminals identified in accordance with North American and IEC conventions

General

Catalog Number	HBL460B6V02
Color	Red
Number Of Poles	3-Pole
Series	Dual Certified UL 1682 & TUV
Specifications	<ul style="list-style-type: none"><li>• Gaskets - Solid Neoprene</li><li>• Housing - Valox®</li><li>• Locking Ring - Reinforced Thermoplastic Polyester</li><li>• Mounting Screws - Stainless Steel</li></ul>



Style  
Type  
UPC

- Retainer - High-Impact Thermoset
- Standard Service
- Watertight Inlet
- 783585372518

Electrical Ratings

Amperage Rating	60/63 A
Current / Amperage Rating	60/63 A
Voltage Rating	380-415 VAC
Voltage Rating Description	380-415 VAC

Conductor Related

Number Of Wires	4-Wire
-----------------	--------

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"><li>• CSA Certified File LR280C</li><li>• UL Classified to IEC 60309-1 IEC 60309-2</li><li>• UL Listed to UL1682</li></ul>
----------------------	--

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog Page - WDK G-13 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Engineering Drawing - HBL460B6V02 AutoCAD Drawing](#)
- [Installation Manuals - WIRING\\_PD1304\\_INSTALLINST](#)
- [Literature - PULP & PAPER SOLUTIONS](#)
- [Literature - Pulp & Paper Solutions](#)
- [Sales Drawings - WDK\\_HBL460B6V02\\_DRAWING\\_PDF](#)
- [Specifications - Wiring HBL460B6V02 Specification Sheet](#)
- [Warranty - Industrial & Commercial Products](#)