

EdgeConnect™ Twist-Lock®
Locking Devices, 15A 125V, Black

By Hubbell Wiring Device-Kellems
Catalog # [HBL4700ST](#)

Locking Devices, EdgeConnect™ Twist-Lock®, Industrial, Duplex
Receptacle, 15A 125V, 2-Pole 3-Wire Grounding, L5-15R,
Screwless Terminal, Black

Features

- Faster termination time
- No need for screwdriver and torque wrench
- Spring Termination eliminates strand relaxation
- Funnel shaped wire entry for ease of termination.

Application

Industrial

General

Catalog Number	HBL4700ST
Color	Black
Contact	Brass
Environmental Conditions	IP20 Suitability
Flammability	HB or better per UL94/CSA 22.2 No.0.17
Material	Nylon
Mounting Type	Screw Mount
Number Of Poles	2
Series	EdgeConnect™
Size	Standard Sized Product
Style	Locking Devices
Temperature Rating	Maximum Continuous 75°C, Minimum -40°C (w/o impact)
Type	Receptacle
UPC	783585730899

Electrical Ratings



Current / Amperage Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 VAC

Conductor Related

Number Of Wires	3
-----------------	---

Certifications And Compliance

Industry Standard(s)	Listed to UL 498, Fed.Spec. W- C-596, Certified to CSA C22.2 No.42
Nema Rating	L5-15R

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - WDK B-13 Catalog Page](#)
[Installation Manuals - HUBBELL EDGEConnect® SCREWLESS
TERMINATION DUPLEX RECEPTACLES](#)
[Literature - EdgeConnect™ Technology](#)
[Literature - EdgeConnect™ Termination vs Standard Push Wire](#)
[Sales Drawings - M-14768](#)
[Specifications - HBL4700ST](#)
[Warranty - Industrial & Commercial Products](#)