

Delivery Systems, Replacement Threaded Plug for HBL5236, Brass

By Hubbell Wiring Device-Kellems Catalog # HBL5236PLUG

Delivery Systems, Replacement Threaded Plug for HBL5236, Brass



General

Color Brass
Horsepower - Maximum 0.5

UPC 783585445458

Dimensions

Weight 0 lb

Electrical Ratings

Amperage Rating 15 A
Current / Amperage Rating 15 A
Current Rating 15 A
Voltage Rating 125 V
Voltage Rating Description 125 V

Certifications and Compliance

Nema Rating 5-15R

Logistics

Carton Quantity 10

Product Assets

Catalog Page - Wiring A-46 Catalog page Catalogs - Wiring Full Catalog Warranty - Industrial & Commercial Products

Related Products

HBL6236 - Straight Blade Devices, Display Type Receptacle, Single, Floor Box for Wood Floors, 15A 125V, 2P 3W, Brass HBL5235 - Straight Blade Devices, Miscellaneous Receptacles, Clock Hanger, brown with Stainless steel plate, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Brown.

HBL5236 - Straight Blade Devices, Miscellaneous Receptacles, Display type, brown phenolic, blank flush plug, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Brass.

HBL5236M2 - Straight Blade Devices, Miscellaneous Receptacles, Display Case, 15A 125V, 2-Pole 3- Wire Grounding, 5-15R, Replacement Receptacle for HBL5236, Brown

