

EdgeConnect™, Straight Blade Devices, Plug, Industrial/Commercial Grade, 2- Pole 3-Wire Grounding, 15A 125V, 5- 15P, Black and White

By Hubbell Wiring Device-Kellems
Catalog # [HBL5266CST](#)



EdgeConnect™, Straight Blade Devices, Plug,
Industrial/Commercial Grade, 2-Pole 3-Wire Grounding, 15A
125V, 5-15P, Black and White

Features

- Spring termination for a faster and more secure terminal connection
- Ribbed housing is impact and chemical resistant
- Superior cord grip design protects terminations from excess strain
- Accepts #14 - #10AWG, solid or stranded

Application

Extra Heavy Duty Industrial/Commercial Grade

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - UL 94 V-2
- Environmental - Operating Temperatures - Maximum continuous 75°C, minimum -40°C (w/o impact)
- Mechanical - Product Identification - Ratings are a permanent part of the device
- Mechanical - Terminal Accommodation - #14-#10 AWG copper stranded or solid conductor only
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

General

| | |
|------------------------------|---|
| Catalog Number | HBL5266CST |
| Color | Black and White |
| Cord Range | 0.230"-0.720"(5.8-18.3) |
| EU RoHS Indicator | Contact Manufacturer |
| Environmental Conditions | Indoor Dry Unless Protected By Additional Means |
| Horsepower - Maximum | 0.5 |
| Insulation | Insulated Body |
| Item Type | Insulgrip® Plug |
| Material | Nylon |
| Material - Mounting Hardware | Cord Mounted |

| | |
|-----------------------|---|
| Number Of Poles | 2-Pole |
| Operating Temperature | Maximum continuous 75°C and minimum without Impact -40 °C |
| Series | EdgeConnect™ |
| Size | 3.28 in x 1.41 in x 1.09 in |
| Specifications | Blade Holder - Nylon, Retainer - Polycarbonate, Cover - Nylon, Cord Clamp - Nylon, Contact Blades - Copper Alloy, Spring - Stainless Steel, Plunger - Nylon, Drive/Assembly/Cord Clamp Screws - Steel |
| Style | Standard |
| Temperature Rating | Maximum continuous 75°C; minimum -40°C (w/o impact) |
| Type | Plugs |
| UPC | 783585964768 |

Dimensions

| | |
|--------------|------------------------|
| Display Size | Standard Sized Product |
| Weight | 0.2 lb |

Electrical Ratings

| | |
|---------------------------|---------------------------|
| Connectivity | Spring Termination |
| Current / Amperage Rating | 15 A |
| Dielectric Strength | Withstands 2,000V minimum |
| Phase | Single Phase |
| Voltage Rating | 125 V |

Conductor Related

| | |
|----------------------|----------------------|
| Conductor Range | #14 AWG to #10 AWG |
| Cord Type | All Listed Portables |
| Number Of Wires | 3-Wire |
| Number of Conductors | 3-Wire Grounding |
| Wire Size | #14 AWG to #10 AWG |

Certifications And Compliance

Industry Standard(s)

- CSA Certified to C22.2 No. 42 File 280
- Fed. Spec. W-C596G
- NEMA® WD-6 Compliant

Nema Rating

5-15P

Logistics

Carton Quantity

10

Product Assets

[Catalog Page - WDK A-38 Catalog Page](#)

[Catalogs - WDK Catalog Full 2024](#)

[Installation Manuals - PD3057](#)

[Literature - EdgeConnect™ Technology FAQ](#)

[Literature - EdgeConnect™ Technology](#)

[Literature - EdgeConnect™ Termination vs Standard Push Wire](#)

[Sales Drawings - M14563](#)

[Specifications - HBL5266CST](#)

[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved
WDK-HBL5266CST-SPEC-EN | REV 3/2025