



# Straight Blade Connector Body, Insulgrip Heavy Duty, Industrial/Commercial, Straight, 2- Pole 3-Wire Grounding, 15A 125V, 5-15R, Black, Single Pack

By Hubbell Wiring Device-Kellems  
Catalog # [HBL5269CM2](#)



Straight Blade Devices, Female Connector Body, Insulgrip Heavy Duty, Industrial/Commercial Grade, Straight, 2- Pole 3- Wire Grounding, 15A 125V, 5-15R, Black, Single Pack

## Features

- Individual wiring terminals completely enclosed
- Powerful, offsetting cord grips clamp on individual conductors
- Fast lead assembly screws
- Beveled housing prevents snagging

## Application

Heavy Duty Industrial

## General

Color	Black
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	Insulgrip
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Wiring Device-Kellems
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.
UPC	783585848525

## Dimensions

Display Size	Standard
--------------	----------

## Electrical Ratings

Amperage Rating	15 A
Connectivity	Screw Terminals
Current / Amperage Rating	15 A
Current Rating	15 A
Voltage Rating	125 VAC

## Conductor Related

Conductor Range	#14 AWG to #12 AWG
Number Of Conductors	3-Wire Grounding

## Certifications and Compliance

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

Engineering Drawing - [HBL5269CM2 AutoCAD Drawing](#)  
Installation Manuals - [WIRING\\_PD2437\\_INSTALLINST](#)  
Installation Manuals - [WIRING\\_PD1214\\_INSTALLINST](#)  
Literature - [WIRING\\_WLFVM034](#)  
Literature - [Insulgrip® Straight Blade and Twist-Lock® Devices](#)  
Literature - [Entertainment Product Solution Guide](#)  
Literature - [Pulp & Paper Solutions](#)  
Sales Drawings - [WDK\\_HBL5269CM2\\_DRAWING\\_PDF](#)  
Warranty - [Industrial & Commercial Products](#)

## Related Products

[HBL5278C](#) - Straight Blade Devices, Male Inlets, Flanged, Industrial/Commercial, 15A 125V, 2-Pole 3-Wire Grounding, 5-15P, White, Single Pack  
[HBL5266CA](#) - Straight Blade Devices, Male Plug, Insulgrip Heavy Duty, Industrial/Commercial Grade, Angled, 2-Pole 3-Wire Grounding, 15A 125V, 5-15P and White  
[HBL5269EBK](#) - Straight Blade Devices, Female Connector Body, Insulgrip Heavy Duty, Industrial/Commercial Grade, Straight, 15A 125V, 5-15R, Extra Large  
[HBL5269CBL](#) - Straight Blade Connector Body, Insulgrip HeavyDuty, Industrial/Commercial, 2-Pole 3-Wire Grounding, 15A 125V, 5-15R, Blue and White, Single Pack  
[HBL5266CBL](#) - Straight Blade Male Plug, Insulgrip Heavy Duty, Industrial/Commercial, Straight, 2-Pole 3- Wire Grounding, 15A 125V, 5-15P, Blue/White, Single Pack

**Certifications and Compliance**

Nema Rating

5-15R



**A proud member of the Hubbell Family.**

©2023 Hubbell Incorporated. All rights reserved.  
WDK-HBL5269CM2-SPEC-EN | REV 4/2023