

Straight Blade Connector Body, Insulgrip Heavy Duty, Industrial/Commercial, Straight, 2- Pole 3-Wire Grounding, 15A 125V, 5- 15R, Black, Single Pack



By Hubbell Wiring Device-Kellems
Catalog # [HBL5269CM2](#)

Straight Blade Devices, Female Connector Body, Insulgrip Heavy Duty, Industrial/Commercial Grade, Straight, 2- Pole 3-Wire Grounding, 15A 125V, 5-15R, Black, Single Pack

Features

- Individual wiring terminals completely enclosed
- Powerful, offsetting cord grips clamp on individual conductors
- Fast lead assembly screws
- Beveled housing prevents snagging

Application

Heavy Duty Industrial

General

Catalog Number	HBL5269CM2
Color	Black
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	Insulgrip
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Wiring Device-Kellems
Series	Insulgrip
Style	Standard
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.
Type	Connector Body
UPC	783585848525

Dimensions

Display Size	Standard
--------------	----------

Electrical Ratings

Amperage Rating	15 A
Connectivity	Screw Terminals
Current / Amperage Rating	15 A
Current Rating	15 A
Voltage Rating	125 VAC

Conductor Related

Conductor Range	#14 AWG to #12 AWG
Number of Conductors	3-Wire Grounding

Certifications And Compliance

Nema Rating	5-15R
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	10
Pallet Quantity	3600

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Engineering Drawing - HBL5269CM2 AutoCAD Drawing](#)
[Installation Manuals - WIRING_PD2437_INSTALLINST](#)
[Installation Manuals - WIRING_PD1214_INSTALLINST](#)
[Literature - PULP & PAPER SOLUTIONS](#)
[Literature - Insulgrip® Straight Blade and Twist-Lock® Devices](#)
[Literature - Pulp & Paper Solutions](#)
[Literature - Entertainment Product Solution Guide](#)
[Sales Drawings - WDK_HBL5269CM2_DRAWING_PDF](#)
[Specifications - HBL5269CM2](#)
[Warranty - Industrial & Commercial Products](#)