

Plug In Adapter, 15A 125V Crow
Foot to 5- 15R

By Hubbell Wiring Device-Kellems
Catalog # [HBL5289](#)



Plug In Adapter, 15A 125V Crow Foot to 5- 15R

Features

- 15A 125V Crow Foot to 5- 15R

General

Catalog Number	HBL5289
Color	White
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Plug-In Adapter
Material	Thermoplastic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Wiring Device-Kellems
Specifications	<ul style="list-style-type: none">Female end - 3 Wire 15A, 125VMale end - 3 wire crow foot 15A, 125V bladesProduct Type - Plug-In Adapters
UPC	783585809175

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Electrical Ratings

Amperage Rating	15 A
Connectivity	Screw Terminals
Current / Amperage Rating	15 A
Current Rating	15 A
Phase	Single Phase
Voltage Rating	Multi-Rated kV
Wattage	2500 Max

Conductor Related

Number Of Wires	3-Wire Grounding
Wire Size	#14 AWG to #12 AWG

Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
Nema Rating	Non-NEMA

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - WDK BB-4 Catalog Page](#)
[Catalogs - WDK Catalog Full 2024](#)
[Specifications - HBL5289](#)
[Warranty - Industrial & Commercial Products](#)

