

PS,IEC,INLT,4P5W,30A 200/346-
240/415V,V0

By Hubbell Wiring Device-Kellems
Catalog # [HBL530B6V02](#)

PS,IEC,INLT,4P5W,30A 200/346-240/415V,V0

Features

- Solid one-piece pins for reliable electrical contact
- Gasketed sealing ring provides watertight seal
- Raised collar surrounds each phase pin

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstand 3000V AC
- Electrical - Max. Working Voltage - 600V RMS
- Environmental - Flammability - HB or better per UL 94 or CSA C22.2 No. 0.17
- Environmental - Ingress Protection - IP67 Suitability
- Environmental - Moisture Resistance - Watertight per IEC 60309-1
- Environmental - Operating Temperatures - Maximum Continuous 75°C
- Minimum - 40°C w/o impact
- Mechanical - Impact Resistance - Per CSA C22.2 No. 182.1 / UL1682
- Mechanical - Product Identification - Ratings are a permanent part of the device housing
- Mechanical - Terminal Identification - Terminals identified in accordance with North American and IEC conventions

General

Catalog Number	HBL530B6V02
Color	Red
Number Of Poles	4-Pole
Series	Dual Certified UL 1682 & TUV
Specifications	<ul style="list-style-type: none">• Gaskets - Solid Neoprene• Housing - Valox®• Locking Ring - Reinforced Thermoplastic Polyester



Style	• Mounting Screws - Stainless Steel
Type	• Retainer - High-Impact Thermoset
UPC	Standard Service Watertight Inlet 783585155487

Electrical Ratings

Amperage Rating	30/32 A
Current / Amperage Rating	30/32 A
Voltage Rating	200/346-240/415 VAC
Voltage Rating Description	200/346-240/415 VAC

Conductor Related

Number Of Wires	5-Wire
-----------------	--------

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• CSA Certified File LR280C• UL Classified to IEC 60309-1 IEC 60309-2• UL Listed to UL1682
----------------------	--

Product Assets

[Catalog Page - WDK G-13 Catalog Page](#)
[Catalogs - WDK Catalog Full 2024](#)
[Engineering Drawing - HBL530B6V02 AutoCAD Drawing](#)
[Installation Manuals - WIRING_PD1304_INSTALLINST Literature - PULP & PAPER SOLUTIONS](#)
[Literature - Pulp & Paper Solutions](#)
[Sales Drawings - WDK_HBL530B_DRAWING_PDF](#)
[Specifications - Wiring HBL530B6V02 Specification Sheet](#)
[Warranty - Industrial & Commercial Products](#)