

Hubbell Wiring Device Kellems, IEC
Pin and Sleeve, Inlet, 30/32A 220-
415V, 3-Pole 4-Wire Grounding,
4X/IP69K

By Hubbell Wiring Device-Kellems
Catalog # [HBL530B6W](#)

Hubbell Wiring Device Kellems, IEC Pin and Sleeve, Inlet,
30/32A,220-415V, 3-Pole 4-Wire Grounding, 4X/IP69K

Features

- Rugged one-piece housing
- Thermoset polyester contact carrier
- Solid one-piece pins for reliable electrical contact

General

Catalog Number	HBL530B6W
Color	Red
EU RoHS Indicator	Contact Manufacturer
Number Of Poles	4-Pole
Series	Advantage Switch-Rated
Style	IP69k NEMA 4X
Type	Watertight Mating Inlet
UPC	783585574578

Electrical Ratings

Amperage Rating	30/32 A
Current / Amperage Rating	30/32 A
Voltage Rating	<ul style="list-style-type: none">• 200/346-240/415 V• 220/380-240/415 V
Voltage Rating Description	200/346-240/415 V;220/380-240/415 V



Conductor Related

Number Of Wires	5-Wire
-----------------	--------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog Page - WDK G-6 Catalog Page](#)
- [Catalog Page - WDK G-10 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Engineering Drawing - HBL530B6W AutoCAD Drawing](#)
- [Installation Manuals - WIRING_PD1304_INSTALLINST](#)
- [Literature - Advantage™ Series Switch-Rated IEC Pin & Sleeve Devices](#)
- [Literature - IEC Pin & Sleeve Devices](#)
- [Literature - PULP & PAPER SOLUTIONS](#)
- [Literature - Pulp & Paper Solutions](#)
- [Literature - Dual-Certified IEC Pin & Sleeve Devices](#)
- [Sales Drawings - WDK_HBL530B6W_DRAWING_PDF](#)
- [Specifications - Wiring HBL530B6W Specification Sheet](#)
- [Warranty - Industrial & Commercial Products](#)
- [Video - Advantage Series Switch-Rated Pin & Sleeve](#)

