

EdgeConnect™ Single Receptacle,
Tamper Resistant, 20A, 125V, Black

By Hubbell Wiring Device-Kellems
Catalog # [HBL5361STBKTR](#)

EdgeConnect™ Single Straight Blade Receptacle, Screwless
Termination Technology, Industrial, Tamper Resistant, 20A Black

Features

- Color coded plungers for simpler installation
- Accepts 14-10 AWG solid or stranded wire for any application
- Reduce your installation time and move on to your next job faster
- Easily rewire by using built in leverage points to life plungers with small screwdriver

Application

Spring clamp terminal strengthens over time providing a more reliable connection.

General

| | |
|----------------|-------------------|
| Catalog Number | HBL5361STBKTR |
| Color | Black |
| Series | EdgeConnect™ |
| Style | Tamper Resistant |
| Type | Single Receptacle |
| UPC | 783585966007 |

Electrical Ratings

| | |
|-----------------|-------|
| Amperage Rating | 20 A |
| Voltage Rating | 125 V |



Conductor Related

| | |
|-----------|----------------------------|
| Wire Size | 14-10AWG Solid or Stranded |
|-----------|----------------------------|

Certifications And Compliance

| | |
|----------------------|---|
| Industry Standard(s) | UL Listed to UL498 File No. E2186, Certified to CSA 22.2, No. 42 File 285, NEMA® WD-6 Compliant |
| Nema Rating | NEMA® WD-6 Compliant |

Logistics

| | |
|-----------------|----|
| Carton Quantity | 10 |
|-----------------|----|

Product Assets

- [Installation Manuals - HUBBELL EDGEConnect™ SCREWLESS TERMINATION SINGLE RECEPTACLES](#)
- [Literature - EdgeConnect™ Technology FAQ](#)
- [Literature - EdgeConnect™ Technology](#)
- [Literature - EdgeConnect™ Termination vs Standard Push Wire](#)
- [Sales Drawings - M-14631](#)
- [Specifications - HBL5361STBKTR](#)
- [Video - Hubbell® EdgeConnect™ Technology](#)