

EdgeConnect™, Duplex Receptacle,
Industrial Grade, Weather Resistant,
2-Pole 3-Wire, 20A 125V, 5-20R,
Screwless Terminal, Red

By Hubbell Wiring Device-Kellems
Catalog # [HBL5362STRWR](#)



Straight Blade Devices, EdgeConnect™ , Duplex Receptacle,
Industrial Grade, Weather Resistant, 2-Pole 3-Wire, 20A 125V, 5-
20R, Screwless Terminal, Red

Features

- Back wired screwless termination for faster termination time
- No need for screwdriver and torque wrench
- Spring Termination eliminates strand relaxation
- Triple and Double Wipe Contacts
- Easy access split circuit tab

General

Catalog Number	HBL5362STRWR
Color	Red
Item Type	Receptacle
Listings	Terminals Identified in Accordance with UL 498 and CSA
Material	Thermoplastic/C
Number Of Poles	2-Pole
Series	EdgeConnect™
Size	3.28x1.58x1.38
Style	Finder Groove Face
Temperature Rating	Maximum continuous 75°C; minimum -40°C (w/o impact)
Type	Weather Resistant
UPC	783585729343

Electrical Ratings

Current / Amperage Rating	20 A
Dielectric Strength	Withstands 2,000V minimum
Interrupt Rating	Certified for current interrupting at full rated current A

Voltage Rating125 V

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 (Solid and Stranded) - #10 (Stranded) Copper Wire Only

Certifications And Compliance

Industry Standard(s)	• UL Listed to UL498 File No. E2186 • Certified to CSA 22.2 • No. 42 File 285, Fed. Spec. W-C-596, NEMA® WD-6 Compliant • UL 94 V-2
Nema Rating	5-20R

Logistics

Carton Quantity10

Product Assets

[Catalog Page - WDK A-22 Catalog Page](#)
[Catalogs - WDK Catalog Full 2024](#)
[Installation Manuals - PD3029](#)
[Literature - EdgeConnect™ Technology FAQ](#)
[Literature - EdgeConnect™ Technology](#)
[Literature - EdgeConnect™ Termination vs Standard Push Wire](#)
[Sales Drawings - M-14695](#)
[Specifications - HBL5362STRWR](#)
[Warranty - Industrial & Commercial Products](#)