

EdgeConnect™, Straight Blade Devices, Plug, Industrial/Commercial Grade, 2-Pole 3-Wire Grounding, 20A 125V, 5-20P, Black and White

By Hubbell Wiring Device-Kellems
Catalog # [HBL5366CST](#)



EdgeConnect™, Straight Blade Devices, Plug, Industrial/Commercial Grade, 2-Pole 3-Wire Grounding, 20A 125V, 5-20P, Black and White

Application

Extra Heavy Duty Industrial/Commercial Grade

General

Color	Black and White
Cord Range	0.230"-0.720"(5.8-18.3)
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	1
Insulation	Insulated Body
Item Type	Insulgrip® Plug
Material	Nylon
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum without Impact -40 °C

Performance	<ul style="list-style-type: none"> Electrical - Current Interrupting - Certified for current interrupting at full rated current Electrical - Dielectric Voltage - Withstands 2,000V minimum Environmental - Flammability - UL 94 V-2 Environmental - Operating Temperatures - Maximum continuous 75°C, minimum -40°C (w/o impact) Mechanical - Product Identification - Ratings are a permanent part of the device Mechanical - Terminal Accommodation - #14-#10 AWG copper stranded or solid conductor only Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA
-------------	---

Series	EdgeConnect™
Size	3.28 in x 1.41 in x 1.09 in

Dimensions

Display Size	Standard Sized Product
Weight	0.2 lb

Electrical Ratings

Connectivity	Spring Termination
Current / Amperage Rating	20 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 V

Conductor Related

Conductor Range	#14 AWG to #10 AWG
Cord Type	All Listed Portables
Number Of Wires	3-Wire
Number of Conductors	3-Wire Grounding
Wire Size	#14 AWG to #10 AWG

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"> CSA Certified to C22.2 No. 42 File 280 Fed. Spec. W-C596G NEMA® WD-6 Compliant UL Listed to UL498 File E1706
----------------------	---

Nema Rating	5-20P
-------------	-------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - WDK A-38 Catalog Page](#)
[Catalogs - WDK Catalog Full 2024](#)
[Installation Manuals - PD3057](#)
[Literature - EdgeConnect™ Technology FAQ](#)
[Sales Drawings - M14563](#)
[Warranty - Industrial & Commercial Products](#)

Style	Standard
Temperature Rating	Maximum continuous 75°C; minimum -40°C (w/o impact)
Type	Plugs
UPC	783585964812



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK-HBL5366CST-SPEC-EN | REV 6/2024