

**HUBBELL**  
Wiring Device-Kellems

**EdgeConnect™, Straight Blade  
Devices, Connector,  
Industrial/Commercial Grade, 2-  
Pole 3-Wire Grounding, 20A 125V,  
5-20R, Black and White**

By Hubbell Wiring Device-Kellems  
Catalog # [HBL5369CST](#)

EdgeConnect™, Straight Blade Devices, Connector,  
Industrial/Commercial Grade, 2-Pole 3-Wire Grounding, 20A  
125V, 5-20R, Black and White



## General

Catalog Number	HBL5369CST
Color	Black and White
Cord Range	0.230"-0.720"(5.8-18.3)
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	1
Insulation	Insulated Body
Item Type	Insulgrip® Connector
Material	Nylon
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	Electrical - Current Interrupting - Certified for current interrupting at full rated current
	Electrical - Dielectric Voltage - Withstands 2,000V minimum
	Environmental - Flammability - UL 94 V-2
	Environmental - Operating Temperatures - Maximum continuous 75°C, minimum -40°C (w/o impact)
	Mechanical - Product Identification - Ratings are a permanent part of the device
	Mechanical - Terminal Accommodation - #14-#10 AWG copper stranded or solid conductor only
	Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA
Series	EdgeConnect™
Size	3.28 in x 1.41 in x 1.09 in
Style	Standard
Temperature Rating	Maximum continuous 75°C; minimum -40°C (w/o impact)
Type	Connectors
UPC	783585965383

## Dimensions

Display Size	Standard Sized Product
Weight	0.2 lb

## Electrical Ratings

Connectivity	Spring Termination
Current / Amperage Rating	20 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 V

## Conductor Related

Conductor Range	#14 AWG to #10 AWG
Cord Type	All Listed Portables
Number Of Wires	3-Wire
Number of Conductors	3-Wire Grounding
Wire Size	#14 AWG to #10 AWG

## Certifications And Compliance

Industry Standard(s)	CSA Certified to C22.2 No. 42 File 280
	Fed. Spec. W-C596G
	NEMA® WD-6 Compliant
	UL Listed to UL498 File E1706
Nema Rating	5-20P

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalog Page - WDK A-39 Catalog Page](#)  
[Catalogs - WDK Catalog Full 2024](#)  
[Installation Manuals - PD3069\\_Installation Manual](#)  
[Literature - EdgeConnect™ Termination vs Standard Push Wire](#)  
[Literature - EdgeConnect™ Technology](#)  
[Literature - EdgeConnect™ Technology FAQ](#)  
[Sales Drawings - M14757](#)  
[Warranty - Industrial & Commercial Products](#)



A proud member of the Hubbell Family.