

Heavy Duty Products, IEC Pin and Sleeve
Devices, Industrial Grade, Female Connector,
60A 4-Pole 5-Wire Grounding, Red, 4X and
IP69k, 1" NPT Liquidtight Threading

By Hubbell Wiring Device-Kellems
Catalog # [HBL560C6WLT100](#)

Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade,
Female Connector, 60/63 A, 200/346-240/415 V;220/380-240/415 V, 4-
Pole 5-Wire Wire Grounding, Terminal Screws, Red, 4X and IP69k

Features

- Insulated Non-Metallic housing
- Color coded housings by voltage for easy identification
- Corrosion-resistant self-closing gasketed cover

Application

High Ampacity Watertight Connections

Specifications

Industry Standard(s)	• CSA Certified File LR280C • UL Classified to IEC 60309-1 IEC 60309-2 • UL Listed to UL1682
Environmental Conditions	Watertight

Conductor

Conductor Range	#8 AWG to #2 AWG
-----------------	------------------

Current

Connectivity	Pressure Terminal Screws
Dielectric Strength	Withstands 3000V Minimum in



Current / Amperage Rating	60 A
Dimensions	
Weight	2.65 lb.
Display Size	Standard Sized Product

General

Color	Red
Style	Standard Service
UPC	783585714752
Type	Watertight Connector Body
Insulation	Insulated Body
Item Type	Standard
Series	HBL Heavy Duty

Logistics

Pallet Quantity	150
Carton Quantity	10

Product Assets

[Catalog Page \[English\]](#)
[Installation Manual \[French, English\]](#)