

Heavy Duty Products, IEC Pin and Sleeve
Devices, Industrial Grade, Female Connector
Body, 60A 3-Phase Wye 277/480V AC,
Watertight, 3/4" NPT Liquidtight Threading

By Hubbell Wiring Device-Kellems
Catalog # [HBL560C7WLT34](#)

Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade,
Female Connector Body, 60A 3-Phase Wye 277/480V AC, 4-Pole 5-Wire
Grounding, Terminal Screws, Red, Watertight

Features

- Insulated Non-Metallic housing
- Color coded housings by voltage for easy identification
- Corrosion-resistant self-closing gasketed cover

Application

High Ampacity Connections

Performance

Electrical - Current Interrupting - Certified for current interrupting at full
rated current, Electrical - Dielectric Voltage - Withstand 3000V AC,
Electrical - Max. Working Voltage - 600V RMS, Environmental -
Flammability - HB or better per UL 94 or CSA C22.2 No. 0.17,
Environmental - Ingress Protection - IP67 Suitability, Environmental -
Moisture Resistance - Watertight per IEC 60309-1, Environmental -
Operating Temperatures - Maximum Continuous 75°C, Minimum - 40°C
w/o impact, Mechanical - Impact Resistance - Per CSA C22.2 No. 182.1 /
UL1682, Mechanical - Product Identification - Ratings are a permanent
part of the device housing, Mechanical - Terminal Identification -
Terminals identified in accordance with North American and IEC
conventions

Specifications

Nema Rating	Non-NEMA
Industry Standard(s)	• CSA Certified File LR280C • UL Classified to IEC 60309-1 IEC 60309-2 • UL Listed, File E146033
Environmental Conditions	Watertight

Conductor

Number Of Poles	4-Pole
Conductor Range	#8 AWG to #2 AWG
Number Of Conductors	5-Wire Grounding
Number Of Wires	5-Wire

Current



*Representative Image

Voltage Rating Description	3 Phase Y 277/480 VAC
Connectivity	Pressure Terminal Screws
Dielectric Strength	Withstands 3000V Minimum in
Current / Amperage Rating	60 A

Dimensions

Weight	3.5 lb.
Display Size	Standard

General

Specifications	• Cord Clamps - Reinforced Thermoplastic Polyester • Covers - Reinforced Thermoplastic Polyester • Gaskets - Solid Neoprene • Glands - Solid Neoprene • Housing - Zytel® ST801 Nylon
Color	Red
Style	Standard Service
UPC	783585714721
Type	Watertight Connector Body
Material - Mounting Hardware	Cord Mounted
Insulation	Insulated Body
Item Type	Standard
Series	HBL Heavy Duty

Logistics

Pallet Quantity	1
Carton Quantity	10

Operational

Temperature Rating	• Maximum Continuous: 75° C • Minimum Continuous: -40° C w/o impact, -25° with impact.
--------------------	--

Product Assets

[Catalog Page \[English\]](#)
[Installation Manual \[French, English\]](#)