

EdgeConnect™ Single Receptacle, 15A, 250V, Light Almond

By Hubbell Wiring Device-Kellems

Catalog # [HBL5661STLA](#)

EdgeConnect™ Single Straight Blade Receptacle, Screwless Termination Technology, Industrial, 15A Light Almond



Features

- Color coded plungers for simpler installation
- Accepts 14-10 AWG solid or stranded wire for any application
- Reduce your installation time and move on to your next job faster
- Easily rewire by using built in leverage points to life plungers with small screwdriver

Application

Spring clamp terminal strengthens over time providing a more reliable connection.

General

Catalog Number	HBL5661STLA
Color	Light Almond
Series	EdgeConnect™
Style	Flat Face
Type	Single Receptacle
UPC	783585966564

Electrical Ratings

Amperage Rating	15 A
-----------------	------

Voltage Rating	250 V
----------------	-------

Conductor Related

Wire Size	14-10AWG Solid or Stranded
-----------	----------------------------

Certifications And Compliance

Industry Standard(s)	UL Listed to UL498 File No. E2186, Certified to CSA 22.2, No. 42 File 285, NEMA® WD-6 Compliant
Nema Rating	NEMA® WD-6 Compliant

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Installation Manuals - HUBBELL EDGEConnect™ SCREWLESS TERMINATION SINGLE RECEPTACLES](#)
[Literature - EdgeConnect™ Technology](#)
[Literature - EdgeConnect™ Termination vs Standard Push Wire](#)
[Sales Drawings - M-14631](#)
[Specifications - HBL5661STLA](#)