

# Adapter, Marine, Molded, Straight Blade, 30A 125V Locking Female L5-30R to 15A 125V 5-15P Straight Blade Male, White

By Hubbell Wiring Device-Kellems  
Catalog # [HBL61CM22W](#)



Adapter, Marine, Molded, Straight Blade, 30A 125V Locking Female L5-30R to 15A 125V 5-15P Straight Blade Male, White

## Features

- New quick connect with backwards compatibility

## General

Application	Straight Adapter
Catalog Number	HBL61CM22W
Color	White
EU RoHS Indicator	No
Insulation	Insulated Body
Item Type	Adapters
Material	Composite
Number Of Pins	Male- 15A 125V Straight Blade
OEM Brand Name	Hubbell Wiring Device-Kellems
Operating Temperature	Max Continuous- 75 Degrees C, Minimum- -40 Without Impact
Performance	Environmental - Moisture Resistance - IP55 Suitability
Receptacle Type	Female- 30A 125V Twist-Lock®
UPC	783585519401

## Electrical Ratings

Amperage Rating	30 A
Current / Amperage Rating	30 A
Current Rating	30 A
Voltage Rating	125 VAC
Wattage	3750

## Certifications And Compliance

Standards - RoHS Compliance CM  
Status

## Logistics

Carton Quantity 10

## Product Assets

[Catalog Page - WDK AA-29 Catalog Page](#)  
[Catalog Page - WDK AA-28 Catalog Page](#)  
[Catalogs - WDK Catalog Full 2024](#)  
[Installation Manuals - WIRING\\_PD2030\\_INSTALLINST](#)  
[Literature - Hubbell Marine Full Line Catalog](#)  
[Warranty - Industrial & Commercial Products](#)

