

Adapter, Marine, Molded, Straight Blade, Yellow

By Hubbell Wiring Device-Kellems
Catalog # [HBL61CM25](#)



Adapter, Marine, Molded, Straight Blade, Yellow

Features

- New quick connect with backwards compatibility

General

Application	Straight Adapter
Catalog Number	HBL61CM25
Color	Yellow
EU RoHS Indicator	No
Insulation	Insulated Body
Item Type	Adapters
Material	Composite
Number Of Pins	Male- 20A 125V Twist-Lock®
OEM Brand Name	Hubbell Wiring Device-Kellems
Operating Temperature	Max Continuous- 75 Degrees C, Minimum- -40 Without Impact
Performance	Environmental - Moisture Resistance - IP55 Suitability
Receptacle Type	Female- 30A 125V Twist-Lock®
UPC	783585808604

Electrical Ratings

Amperage Rating	30 A
Current / Amperage Rating	30 A
Current Rating	30 A
Voltage Rating	125 VAC
Wattage	3750

Product Assets

- [Catalog Page - WDK AA-29 Catalog Page](#)
- [Catalog Page - WDK AA-28 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Installation Manuals - WIRING_PD2030_INSTALLINST](#)
- [Literature - Hubbell Marine Full Line Catalog](#)
- [Warranty - Industrial & Commercial Products](#)