

## Adapter, Marine, Molded, Straight Blade, Yellow

By Hubbell Wiring Device-Kellems

Catalog # [HBL61CM54](#)



Adapter, Marine, Molded, Straight Blade

### Features

- Marine
- Molded
- Straight Blade
- Yellow

### Application

Straight Adapter

### Performance

Environmental - Moisture Resistance - IP55 Suitability

### General

Catalog Number	HBL61CM54
Color	Yellow
EU RoHS Indicator	No
Insulation	Insulated Body
Item Type	Adapters
Material	Composite
Number Of Pins	Male- 15A 125V Straight Blade
OEM Brand Name	Hubbell Wiring Device-Kellems
Operating Temperature	Max Continuous- 75 Degrees C, Minimum- -40 Without Impact
Receptacle Type	Female- 50A 125V Twist-Lock®
Specifications	<ul style="list-style-type: none"><li>• Adapter Style - Straight (Pig Tail)</li></ul>

UPC

- Female End Rating - 50A 125V, 2P3W Twist-Lock®
  - Male End Rating - 15A 125V, 2P3W Straight Blade
  - Poles and Wires - 2 Pole, 3 Wire Grounding
  - Product Type - Adapters
- 783585808611

### Electrical Ratings

Amperage Rating	50 A
Current / Amperage Rating	50 A
Current Rating	50 A
Voltage Rating	125 VAC
Wattage	6250

### Logistics

Carton Quantity	1
-----------------	---

### Product Assets

[Catalog Page - WDK AA-28 Catalog Page](#)  
[Catalog Page - WDK AA-29 Catalog Page](#)  
[Catalogs - WDK Catalog Full 2024](#)  
[Installation Manuals - WIRING\\_PD2030\\_INSTALLINST](#)  
[Literature - Hubbell Marine Full Line Catalog](#)  
[Specifications - HBL61CM54](#)  
[Warranty - Industrial & Commercial Products](#)