

Adapter, Marine, Molded, Straight Blade, 30A 125V Locking Female L5-30R to 50A 125V Locking Male, Yellow

By Hubbell Wiring Device-Kellems Catalog # HBL61CM55





Application

Straight Adapter

General

ColorYellowInsulationInsulated BodyItem TypeAdaptersMaterialComposite

Number Of Pins Male- 50A 125V Twist-Lock®

OEM Brand Name Hubbell Wiring Device-

Kellems

Operating Temperature Max Continuous- 75 Degrees

C, Minimum- -40 Without

Impact

Performance Environmental - Moisture

Resistance - IP55 Suitability

Receptacle Type Female- 30A 125V Twist-Lock®

UPC 783585808628

Electrical Ratings

Amperage Rating 30 A
Current / Amperage Rating 30 A
Current Rating 30 A
Voltage Rating 125 VAC
Wattage 3750

Product Assets

Catalog Page - Wiring_Catalog_BB29_CatPage

Catalogs - Wiring Full Catalog

Installation Manuals - WIRING PD2030 INSTALLINST

Literature - Hubbell Marine Full Line Catalog Warranty - Industrial & Commercial Products

Related Products

HBL63CM70 - Locking Devices, Twist-Lock®, Marine Grade, Receptacle, 50A 125V, 2-Pole 3-Wire Grounding, Non-NEMA, Screw Terminal, Galvanized

HBL61CM25 - Adapter, Marine, Molded, Straight Blade, Yellow HBL61CM08 - Locking Devices, Twist-Lock*, Marine Grade, Ship to Shore Cableset, 30A 125V, 2-Pole 3-Wire Grounding, L5-30, Yellow

HBL61CM22 - Adapter, Marine, Molded, Straight Blade, 30A 125V Locking Female L5-30R to 15A 125V 5-15P Straight Blade Male, Yellow

