

Adapter, Marine, Molded, Straight Blade, Yellow, 30A 125V 2-Pole 3-Wire Grounding Female to 50A 125V, 2-Pole 3- Wire Grounding Locking Male, Yellow



By Hubbell Wiring Device-Kellems Catalog # HBL61CM56

Adapter, Marine, Molded, Straight Blade, 30A 125V 2-Pole 3-Wire Grounding Female to 50A 125V, 2-Pole 3-Wire Grounding Locking Male

Application

Straight Adapter

General

Color	Yellow
Insulation	Insulated Body
Item Type	Adapters
Material	Composite
Number Of Pins	Male- 30A 125V Twist-Lock®
OEM Brand Name	Hubbell Wiring Device- Kellems
Operating Temperature	Max Continuous- 75 Degrees C, Minimum40 Without Impact
Performance	Environmental - Moisture Resistance - IP55 Suitability
Receptacle Type	Female- 50A 125V Twist-Lock®
UPC	783585808635

Electrical Ratings

Amperage Rating	50 A
Current / Amperage Rating	50 A
Current Rating	50 A
Voltage Rating	125 VAC
Wattage	6250

Product Assets

Catalog Page - Wiring_Catalog_BB29_CatPage Catalogs - Wiring Full Catalog Installation Manuals - WIRING_PD2030_INSTALLINST Literature - Hubbell Marine Full Line Catalog Warranty - Industrial & Commercial Products

Related Products

HBL61CM72 - Adapter, Marine, Molded Straight, Yellow HBL61CM53 - Locking Devices, Twist-Lock®, Marine Grade, Ship to Shore Cableset, 50A 125V, 2-Pole 3-Wire Grounding, Non-NEMA, Yellow

HBL26CM10 - Locking Devices, Twist-Lock*, Marine Grade, Flush Receptacle, 30A 125V, 2-Pole 3-Wire Grounding, L5-30R, Screw Terminal, Yellow

HBL61CM54 - Adapter, Marine, Molded, Straight Blade, Yellow

