



Adapter, Marine, Molded, Straight Blade, 30A 125V, 2-Pole 3-Wire Grounding Female to 50A 125/250V, 3-Pole 4-Wire Grounding Locking Male

By Hubbell Wiring Device-Kellems
Catalog # [HBL61CM71](#)



Adapter, Marine, Molded, Straight Blade, 30A 125V, 2-Pole 3-Wire Grounding Female to 50A 125/250V, 3-Pole 4-Wire Grounding Locking Male

Application

Straight Adapter

General

Color	Yellow
Insulation	Insulated Body
Item Type	Adapters
Material	Composite
Number Of Pins	Male- 50A 125/250V Twist-Lock®
OEM Brand Name	Hubbell Wiring Device-Kellems
Operating Temperature	Max Continuous- 75 Degrees C, Minimum- -40 Without Impact
Performance	Environmental - Moisture Resistance - IP55 Suitability
Receptacle Type	Female- 30A 125V Twist-Lock®
UPC	783585808680

Electrical Ratings

Amperage Rating	30 A
Current / Amperage Rating	30 A
Current Rating	30 A
Voltage Rating	125/250 VAC
Wattage	7500

Product Assets

[Catalog Page - Wiring_Catalog_BB29_CatPage](#)
[Catalogs - Wiring Full Catalog](#)
[Installation Manuals - WIRING_PD2030_INSTALLINST](#)
[Literature - Hubbell Marine Full Line Catalog](#)
[Warranty - Industrial & Commercial Products](#)

Related Products

[HBL61CM22W - Adapter, Marine, Molded, Straight Blade, 30A 125V Locking Female L5-30R to 15A 125V 5-15P Straight Blade Male, White](#)
[HBL61CM22 - Adapter, Marine, Molded, Straight Blade, 30A 125V Locking Female L5-30R to 15A 125V 5-15P Straight Blade Male, Yellow](#)
[HBL63CM69 - Locking Devices, Twist-Lock®, Marine Grade, Receptacle, 50A 125/250V, 3-Pole 4-Wire Grounding, Non-NEMA, Screw Terminal, Galvanized](#)
[HBL61CM25 - Adapter, Marine, Molded, Straight Blade, Yellow](#)
[HBL61CM08 - Locking Devices, Twist-Lock®, Marine Grade, Ship to Shore Cableset, 30A 125V, 2-Pole 3-Wire Grounding, L5-30, Yellow](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
WDK-HBL61CM71-SPEC-EN | REV 5/2023