

Adapter, Marine, Molded Straight, Yellow

By Hubbell Wiring Device-Kellems
Catalog # [HBL61CM72](#)



Marine Adapter Molded Straight Blade

Application

Straight Adapter

General

Color	Yellow
EU RoHS Indicator	No
Insulation	Insulated Body
Item Type	Adapters
Material	Composite
Number Of Pins	Male- 50A 125/250V Twist-Lock®
OEM Brand Name	Hubbell Wiring Device-Kellems
Operating Temperature	Max Continuous- 75 Degrees C, Minimum- -40 Without Impact
Performance	Environmental - Moisture Resistance - IP55 Suitability
Receptacle Type	Female- 50A 125V Twist-Lock®
UPC	783585808697

Electrical Ratings

Amperage Rating	50 A
Current / Amperage Rating	50 A
Current Rating	50 A
Voltage Rating	125/250 VAC
Wattage	12500

Certifications And Compliance

Standards - RoHS Compliance CM Status

Logistics

Carton Quantity 1

Product Assets

[Catalog Page - WDK AA-29 Catalog Page](#)
[Catalog Page - WDK AA-28 Catalog Page](#)
[Catalogs - WDK Catalog Full 2024](#)
[Installation Manuals - WIRING_PD2030_INSTALLINST](#)
[Literature - Hubbell Marine Full Line Catalog](#)
[Warranty - Industrial & Commercial Products](#)

