



Wiring Device-Kellems

Adapter, Marine Adapter, Molded "Y", 2) 30A 125V Locking Female L5-30R to 50A 125/250V Locking Male, 4-Pole 4- Wire Grounding, Yellow



By Hubbell Wiring Device-Kellems
Catalog # [HBL64CM54](#)

Marine Adapter, Molded "Y", Two 30A Locking Female to 50A Locking Male

Application

"Y" Adapter

General

Color	Yellow
Insulation	Insulated Body
Item Type	Adapters
Material	Composite
Number Of Pins	Male- 50A 125/250V Twist-Lock®
OEM Brand Name	Hubbell Wiring Device-Kellems
Operating Temperature	Max Continuous- 75 Degrees C, Minimum- -40 Without Impact
Performance	Environmental - Moisture Resistance - IP55 Suitability (Connectors)
Receptacle Type	Female- 30A 125V Twist-Lock®
UPC	783585808772

Electrical Ratings

Amperage Rating	30 A
Current / Amperage Rating	30 A
Current Rating	30 A
Voltage Rating	125/250 VAC
Wattage	7500

Product Assets

- [Catalog Page - Wiring_Catalog_BB29_CatPage](#)
- [Catalogs - Wiring Full Catalog](#)
- [Installation Manuals - WIRING_PD2030_INSTALLINST](#)
- [Literature - Hubbell Marine Full Line Catalog](#)
- [Warranty - Industrial & Commercial Products](#)

Related Products

- [HBL64CM55 - Adapter, Marine Adapter, Molded "Y", 2\) 50A 125V Locking Female 2-Pole 3-Wire Grounding to 50A 125/250V, Locking Male 3-Pole 4-Wire Grounding, Yellow](#)
- [HBL63CM69 - Locking Devices, Twist-Lock®, Marine Grade, Receptacle, 50A 125/250V, 3-Pole 4-Wire Grounding, Non-NEMA, Screw Terminal, Galvanized](#)
- [HBL61CM08 - Locking Devices, Twist-Lock®, Marine Grade, Ship to Shore Cableset, 30A 125V, 2-Pole 3-Wire Grounding, L5-30, Yellow](#)
- [HBL64CM56 - Adapter, Marine Adapter, Molded "Y", 2\) 30A 125V Locking Female L5-30R to 30A 125 Locking Male, 2-Pole 3-Wire Grounding, Yellow](#)
- [HBL64CM57 - Adapter, Marine Adapter, Molded "Y", 2\) 30A 125V Locking Connectors to 50A 125V, Locking Plug, Yellow](#)



A proud member of the Hubbell Family.