



Straight Blade Devices, Plug Strip, 6) Receptacles, Metallic Body, 6' Cord

By Hubbell Wiring Device-Kellems
 Catalog # [HBL6MPS](#)



Straight Blade Devices, Plug Strip, 6) Receptacles, Metallic Body, 6' Cord

Features

- Office White color for aesthetics and metal housing
- 6 foot cord
- wire management

Application

Standard Devices

General

Color	Office White
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Indicator(s) Type	LED Indicator
Item Type	Surge Protection Plug Strips
Material	Steel
Material - Mounting Hardware	Portable
Number Of Outlets	6
OEM Brand Name	Hubbell Wiring Device-Kellems
Operating Temperature	32 Deg F to 140 Deg F (0 Deg C to 60 Deg C)
Outlet	Straight Blade 5-15R
Response Time	5
Series	Economy Power Strips (no SPD)
Type	Metallic
UPC	783585120669

Dimensions

Display Size 0 Joules

Electrical Ratings

Connectivity	Plug-In
Current / Amperage Rating	15 A
Current Rating	15 A
Frequency Rating	60 Hz
Phase	Single Phase

Conductor Related

Cord Length 6 ft

Logistics

Carton Quantity 20

Product Assets

- [Catalog Page - Wiring N-9 Catalog page](#)
- [Catalogs - Wiring Full Catalog](#)
- [Engineering Drawing - HBL6MPS AutoCAD Drawing](#)
- [Installation Manuals - WIRING_PD2380_INSTALLINST](#)
- [Literature - SpikeShield® Power Quality Surge Protective Devices](#)
- [Sales Drawings - WDK_HBL6MPS_DRAWING_PDF](#)
- [Warranty - Surge Plug Strips](#)



A proud member of the Hubbell Family.