



Wiring Device-Kellems

Surge Protective Devices, SPIKESHIELD TVSS Plug Strips, Hospital Grade, 15A 125V, 6 Outlet, 350 Joules, 15' Cord, Office White



By Hubbell Wiring Device-Kellems
Catalog # [HBL6PSHG](#)

Surge Protective Devices, SPIKESHIELD TVSS Plug Strips, Hospital Grade, 15A 125V, 6 Outlet, 350 Joules, 15' Cord, Office White

Features

- Yellow color for high visibility and metal housing
- 350 joules, 6 foot cord, wire management

General

EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Indicator(s) Type	LED Indicator
Item Type	Surge Protection Plug Strips
Material	Non-Metallic
Material - Mounting Hardware	Portable
OEM Brand Name	Hubbell Wiring Device-Kellems
Operating Temperature	32 Deg F to 140 Deg F (0 Deg C to 60 Deg C)
Outlet	Straight Blade 5-15R
Performance	<ul style="list-style-type: none"> • Electrical - Max Surge Current - 30.0kA • Electrical - Max. Operating Voltage - 130 • Electrical - Operating Frequency - 50/60Hz • Environmental - Operating Temperature - -40°F to 160°F (-40°C to 70°C)
Response Time	5
UPC	783585451305

Dimensions

Display Size 450 Joules

Electrical Ratings

Amperage Rating	15 A
Connectivity	Plug-In
Current / Amperage Rating	15 A
Current Rating	15 A
Frequency Rating	60 Hz
Phase	Single Phase
Voltage Rating	125 VAC

Logistics

Carton Quantity 10

Product Assets

- [Installation Manuals - WIRING_PD1849_INSTALLINST](#)
- [Sales Drawings - WDK_HBL6PSHG_DRAWING_PDF](#)
- [Warranty - Surge Plug Strips](#)

Related Products

- [HBL6HG6 - Surge Protective Devices, Hospital Grade Outlet Strip, 15A 125V, 6' Cord Length](#)
- [HBL6RPT1520BK - 20A 6 outlet RPT](#)
- [HBL6RPT620BK - 20A 6 outlet RPT](#)
- [HBL6RPT6BK - 15A 6 outlet RPT](#)
- [HBL6HG15 - Surge Protective Devices, Hospital Grade Outlet Strip, 15A 125V, 15' Cord Length](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
WDK-HBL6PSHG-SPEC-EN | REV 5/2023