

Surge Protective Devices,  
SPIKESHIELD TVSS Plug Strips, 15A  
125V, 6 Outlet, 2100 Joules, Remote  
Switch, 6' Cord Office White

By Hubbell Wiring Device-Kellems  
Catalog # [HBL6RSPS2100](#)

Surge Protective Devices, SPIKESHIELD TVSS Plug Strips, 15A  
125V, 6 Outlet, 2100 Joules, Remote Switch, 6' Cord Office White

Features

- Four outlet, 1050 joule SPD features a black housing
- 6 foot cord, 90 degree plug, and two USB ports for charging

Performance

- Electrical - Max Surge Current - 39.0kA
- Electrical - Max. Operating Voltage - 130
- Electrical - Operating Frequency - 50/60Hz
- Environmental - Operating Temperature - -40°F to 160°F (-40°C to 70°C)

General

Catalog Number	HBL6RSPS2100
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Indicator(s) Type	LED Indicator
Item Type	Surge Protection Plug Strips
Material	Non-Metallic
Material - Mounting Hardware	Portable
OEM Brand Name	Hubbell Wiring Device-Kellems
Operating Temperature	32 Deg F to 140 Deg F (0 Deg C to 60 Deg C)
Outlet	Straight Blade 5-15R
Response Time	5
Specifications	<ul style="list-style-type: none"><li>• Color - Off. White</li><li>• Cord Length - 6 Inch</li></ul>



UPC	<ul style="list-style-type: none"><li>• Housing - ABS</li><li>• Joule Rating - 2100</li></ul> 783585120645
-----	--

Dimensions

Display Size	2100 Joules
--------------	-------------

Electrical Ratings

Amperage Rating	15 A
Connectivity	Plug-In
Current / Amperage Rating	15 A
Current Rating	15 A
Frequency Rating	60 Hz
Phase	Single Phase
Voltage Rating	125 VAC

Logistics

Carton Quantity	20
-----------------	----

Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Engineering Drawing - HBL6RSPS2100 AutoCAD Drawing](#)  
[Installation Manuals - WIRING\\_PD2380\\_INSTALLINST](#)  
[Sales Drawings - WDK\\_HBL6RSPS2100\\_DRAWING\\_PDF](#)  
[Specifications - HBL6RSPS2100](#)  
[Warranty - Surge Plug Strips](#)