

# Surge Protective Devices, SPIKESHIELD TVSS Plug Strips, 15A 125V, 6 Outlet, 2100 Joules, Remote Switch, 6' Cord Office White



By Hubbell Wiring Device-Kellems  
Catalog # [HBL6RSPS2100](#)

Surge Protective Devices, SPIKESHIELD TVSS Plug Strips, 15A  
125V, 6 Outlet, 2100 Joules, Remote Switch, 6' Cord Office White

## Features

- Four outlet, 1050 joule SPD features a black housing
- 6 foot cord, 90 degree plug, and two USB ports for charging

## General

|                              |  |
|------------------------------|--|
| EU RoHS Indicator            | Contact Manufacturer   |
| Environmental Conditions     | Indoor Dry Unless Protected By Additional Means                        |
| Indicator(s) Type            | LED Indicator  |
| Item Type                    | Surge Protection Plug Strips   |
| Material                     | Non-Metallic   |
| Material - Mounting Hardware | Portable   |
| OEM Brand Name               | Hubbell Wiring Device-Kellems  |
| Operating Temperature        | 32 Deg F to 140 Deg F (0 Deg C to 60 Deg C)                            |
| Outlet                       | Straight Blade 5-15R   |
| Performance                  | Electrical - Max Surge Current - 39.0kA                                |
|                              | Electrical - Max. Operating Voltage - 130                              |
|                              | Electrical - Operating Frequency - 50/60Hz                             |
|                              | Environmental - Operating Temperature - -40°F to 160°F (-40°C to 70°C) |
| Response Time                | 5  |
| UPC                          | 783585120645   |

## Dimensions

|              |             |
|--------------|-------------|
| Display Size | 2100 Joules |
|--------------|-------------|

## Electrical Ratings

|                           |              |
|---------------------------|--------------|
| Amperage Rating           | 15 A         |
| Connectivity              | Plug-In      |
| Current / Amperage Rating | 15 A         |
| Current Rating            | 15 A         |
| Frequency Rating          | 60 Hz        |
| Phase                     | Single Phase |
| Voltage Rating            | 125 VAC      |

## Logistics

|                 |    |
|-----------------|----|
| Carton Quantity | 20 |
|-----------------|----|

## Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Engineering Drawing - HBL6RSPS2100 AutoCAD Drawing](#)  
[Installation Manuals - WIRING\\_PD2380\\_INSTALLINST](#)  
[Sales Drawings - WDK\\_HBL6RSPS2100\\_DRAWING\\_PDF](#)  
[Warranty - Surge Plug Strips](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
WDK-HBL6RSPS2100-SPEC-EN | REV 6/2024